















4-2299251-1	D	A	1	PROTECTIVE COVER 4POS.	PBT-GF10	BLACK	4	
			1	SEALING 4POS.	MVQ 30	NATURAL	3	
			1	RETAINER 4POS.	PBT-GF15	GREEN	2	
			1	SOCKET HOUSING 4POS.	PBT-GF15	YELLOW	7	
3-2299251-1	C	A	1	PROTECTIVE COVER 4POS.	PBT-GF10	BLACK	4	
			1	SEALING 4POS.	MVQ 30	NATURAL	3	
			1	RETAINER 4POS.	PBT-GF15	GREEN	2	
			1	SOCKET HOUSING 4POS.	PBT-GF15	BLUE	6	
2-2299251-1	B	A	1	PROTECTIVE COVER 4POS.	PBT-GF10	BLACK	4	
			1	SEALING 4POS.	MVQ 30	NATURAL	3	
			1	RETAINER 4POS.	PBT-GF15	GREEN	2	
			1	SOCKET HOUSING 4POS.	PBT-GF15	GREY	5	
1-2299251-1	A	A	1	PROTECTIVE COVER 4POS.	PBT-GF10	BLACK	4	
			1	SEALING 4POS.	MVQ 30	NATURAL	3	
			1	RETAINER 4POS.	PBT-GF15	GREEN	2	
			1	SOCKET HOUSING 4POS.	PBT-GF15	BLACK	1	
TE ORDER-NO.	5	COD	REV 7	QTY	DESCRIPTION	MATERIAL	COLOUR	ITEM



- NOTES
- CODING A AS SHOWN
 - SUITABLE FOR SOCKET CONTACT FOR SINGLE WIRE SEALING: 962885 (DBG 0.2-0.5mm²), 965906 (DBG 0.75mm²)
 - SUITABLE FOR SHROUDED CONNECTION SEE DRAWING: 114-18063-124
 - SUITABLE FOR WIRE SIZE RANGE: TO 0.75mm²
- 5 TE ORDER-NO.
- 6 DATA CODE:WWYY
- 7 PRODUCT REV.

TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16001-140@CENTRIC TO NOMINAL DIMENSION. EDITION 1982-11 SHALL APPLY. Freimaßtoleranzen nach DIN 16001-140@. Es gilt die Ausgabe 1982-11.		THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J.ZONG 22JAN2016	NAME MOS SOCKET HOUSING, ASSY FOR SW5, 4POSN.	RESTRICTED TO
PRODUCT CHARACTERISTICS ACC. QMP EMEA_12 BESONDERE MERKMALE NACH QMP EMEA_12		CHK S.W.ANG 22JAN2016		APVD		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
MATERIAL		FINISH		APPLICATION SPEC		
SEE TALBE		SEE TALBE		WEIGHT	SIZE A1	CAGE CODE
				CUSTOMER DRAWING	DRAWING NO. C=2299251	REV A
				SCALE 5:1	SHEET 1 OF 1	