


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	EH-0394-97	16APR1997	JvL	RB
	B	ER00-0218-03	18JUL2003	TC	YP
	BI	REVISED PER ECO-09-025699	17DEC2009	KK	AEG
	C	MATERIAL COLOR CHANGED FROM BLUE TO BLACK	01JAN2024	SP	JK



	45.72	43.18	18	1-281838-8
	38.10	35.56	15	1-281838-5
5	OBSOLETE	35.56	14	1-281838-4
	30.48	27.94	12	1-281838-2
	25.40	22.86	10	1-281838-0
5	OBSOLETE	22.86	9	0-281838-9
	20.32	17.78	8	0-281838-8
5	OBSOLETE	17.78	7	0-281838-7
	15.24	12.70	6	0-281838-6
	12.70	10.16	5	0-281838-5
	10.16	7.62	4	0-281838-4
	7.62	5.08	3	0-281838-3
	DIM "B"	DIM "A"	NR OF POS.	TE PN

NOTES:

- MATERIAL DESCRIPTION: POCAN B 4225, BLACK 901510 (RAL9011)
  - IDENTIFICATION OF CONTACT CAVITY NR 1
  - PRODUCT ACCORDING TO IEC 603-8
  - ACCEPTS CRIMP CONTACTS 188746-1 OR 188744-1
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. CORRIOU 18JUL2003		
		CHK Y. PETRONIN 18JUL2003		
		APVD M. FURIO 18JUL2003		
DIMENSIONS: mm		PRODUCT SPEC		NAME SINGLE ROW HOUSING FOR HE 13-14 COSI CONTACT
		APPLICATION SPEC		SIZE A3
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT -		CAGE CODE 00779
0 PLC ±0.2		CUSTOMER DRAWING		DRAWING NO C-281838
1 PLC ±0.2		SCALE 5:1		RESTRICTED TO -
2 PLC ±0.2		SHEET 1 OF 1		REV C
3 PLC ±				
4 PLC ±				
ANGLES ±1°				
FINISH -				