



NOTES

- ① N.2 CAVITIES SUITABLE FOR POSITIVE LOCK MKI CONTACTS SRS. .250".
- ② N.3 CAVITIES SUITABLE FOR JUNIOR POWER TIMER CONTACTS

BLACK	PA 6.6 NAT.	282240-1
FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO
THIS DRAWING IS UNPUBLISHED - RELEASE FOR PUBLICATION		
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		
TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE CING. DIA. RANGE	RANGO FILO WIRE RANGE
± 0.3	//	//
ANGOLI CANGLED ± 2°	SCALA (SCALE) 3:1	
AMP AMP ITALIA S.p.A. Corso F.lli Carvi, 15 COLLEGGIO (TORINO)		
DESCRIZIONE (DESCRIPTION) 5 POSITIONS MICRO-RELAY HSG FOR TRUCK		
REV. / REVISIONI (REVISION RECORD)	LOC. / SIZE (CODE NO)	NUMERO (DRAWING NO)
1 WAS P/N 90-51162 C.I. 1991	IA3	C-282240
2 REVISED C.I. 1991	REV.	B
3 REVISED C.I. 1991	FOLIO (SHEET)	1
4 IN PRODUCTION C.I. 1992	DI	1
5 DIMENSION 23.3 ± 0.2 C.I. 1992	COPI	1
6 WAS 23.1 ± 0.2 (I-3155) C.I. 1992		
7		
8		

90-005