


DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



PART NUMBER	L (METER)
0-0349561-1	1.0 -0/+0.1
0-0349561-2	2.0 -0/+0.1
0-0349561-3	3.0 -0/+0.1
0-0349561-4	4.0 -0/+0.1
0-0349561-5	5.0 -0/+0.1
0-0349561-6	6.0 -0/+0.1
0-0349561-7	7.0 -0/+0.1
0-0349561-8	8.0 -0/+0.1
0-0349561-9	9.0 -0/+0.1
1-0349561-0	10.0 -0/+0.1
1-0349561-1	11.0 -0/+0.2
1-0349561-2	12.0 -0/+0.2
1-0349561-3	13.0 -0/+0.2
1-0349561-4	14.0 -0/+0.2
1-0349561-5	15.0 -0/+0.2
1-0349561-6	16.0 -0/+0.2
1-0349561-7	17.0 -0/+0.2
1-0349561-8	18.0 -0/+0.2
1-0349561-9	19.0 -0/+0.2
2-0349561-0	20.0 -0/+0.2
3-0349561-0	30.0 -0/+0.2
4-0349561-0	40.0 -0/+0.5
9-0349561-0	1.5 -0/+0.1
9-0349561-0	9.5 -0/+0.1

NOTES:

- ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300 nm ACC. IEC 874-1
CLAUSE 4.4.7. METHOD 7 EQUILIBRIUM MODE CONDITION
- ACTUAL ATTENUATION SUPPLIED ON TEST RESULT SHEET PER
INDIVIDUALLY PACKED ASSEMBLY
- CABLE INFO:
 - FIBRE CORE: 50 μ m
 - JACKET MATERIAL: LOW SMOKE ZERO HALOGEN
 - JACKET COLOUR: ORANGE
 - OUTER DIAMETER: 2,5 X 5,0 mm

L	DESCRIPTION	QTY	ITEM
7	FO CABLE 50/125 DES TWIN ZIP 2,5mm	-	7
2	WRAP AROUND LABEL, DAT-85	-	6
2	ST BOOT, RED	-	5
2	ST BOOT, BLACK	-	4
4	ST CRIMP EYELET	-	3
4	ST CERAMIC, OVERMOLDED	-	2
4	FERRULE DUST CAP, BLACK	-	1
QTY	PART NUMBER	DESCRIPTION	ITEM
-	-	CUSTOMER DRAWING	FOR REFERENCE ONLY WILL NOT BE UPDATED
-	-	© COPYRIGHT 19 - BY TYCO NEDERLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. TYCO PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION -19-	
-	-	Tyco Electronics Corporation 's-Hertogenbosch, Nederland	
D	EH02-0293-03	SG JVE 26 SEP 03	NAME
C	EH-1194-00	SvP NS 31 OCT 00	
B	EH-0491-98	MN MN 03 APR 98	
LTR.	REVISION RECORD	DR. CHK. DATE	
DR.:	M.NIJHUIS	CHK.:	J.v. EEUWIK
DATE:	03 APR 98	DATE:	26 SEP 03
DS	J.v. EEUWIK	DATE:	26 SEP 03
DWG.No.	C-349561	REV.LTR.	D
SHEET	1 of 1		A2