





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 2018 BY - TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
C		REVISED PER ECR-19-009721	01JUL2019	MG DZ

- 1 THIS HOUSING ACCEPTS RECEPTACLE TERMINAL:
 - REC CONTACT: 177915- [] (AWG #16-#20)
 : 177914- [] (AWG #22-#26)
- 2 MATING CONN. P/N
 - PC BOARD MOUNT(ASS'Y): 179848-[]
- 3 APPLICABLE DOUBLE LOCK PLATE: 316061-1
 * IT SHOULD BE USED CERTAINLY WHEN CABLE ASS'Y
- 4 GENERAL TOLERANCES: ±0.3
- 5 MATERIAL: PA66, UL94V-0.
 COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF
 NON-METALLIC MATERIALSUPPORTING A CURRENT-CARRYING
 CONNECTION DETAILED IN IEC 60335-1,SECTION 30(GWT)



COLOR	PART NUMBER
BLUE	368574-6
YELLOW	368574-4
RED	368574-2
NATURAL	368574-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SC KIM		
DIMENSIONS: mm		CHK BW KANG		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JK SONG	NAME PDL 4P PLUG 6.5mm D/R (GWT)	
0 PLC ±-		PRODUCT SPEC 108-5410	SIZE A3	
1 PLC ±-		APPLICATION SPEC 114-5175	CAGE CODE 00779	DRAWING NO C-368574
2 PLC ±-		WEIGHT -	RESTRICTED TO -	
3 PLC ±-		MATERIAL 5	SCALE 4:1	
4 PLC ±-			SHEET 1 OF 1	
ANGLES ±-		REV C		
FINISH -		CUSTOMER DRAWING		