



REV. 0  
DCO 143947

COIL: @ 25°C	
SET	RESET
975 OHMS ±10%	975 OHMS ±10%
16.0-29.0 VDC NOMINAL VOLTAGE	16.0-29.0 VDC NOMINAL VOLTAGE
8.8 mADC MUST OPERATE	8.8 mADC MUST OPERATE
ENVIRONMENT:	
VIBRATION	10 Hz      3000 Hz      30 g's
SHOCK	150 g's      11 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES: SET AND RESET TIME 4 MS MAX.	
CONTACT BOUNCE 2 MS MAX.	

CUSTOMER DATA SHEET

CONTACT RATING: LOW LEVEL TO 2A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 13OCT2004      CK. J.M.B. 10/13/04

**CII Technologies™**  
advanced control electronic solutions

CUST. C.I.I. STD.	TYPE "3SAM" RELAY
CUST. NO.	

3SAM6074M2