


| LOC | DIST | REV | DATE | BY | APPV |
|-----|------|-----|---------|----|------|
| - | - | U | 6-13-13 | CT | DM |



MAT'L: COPPER ALLOY PER ASTM-B-301
 FINISH: GOLD PLATED .000050 MIN THK
 PER ASTM-B-488 OVER NICKEL PLATE
 .000050 MIN THK PER AMS-QQ-N-290

| REMARKS | DIM G | DIM F | PART NUMBER |
|---------|-----------|-----------|-------------|
| -- | .776 | .079-.083 | 3-448140-0 |
| 3 | .617±.010 | .087 MAX | 2-448140-7 |
| -- | .576 | .079-.083 | 2-448140-6 |
| 3 5 | .617 | .087 MAX | 2-448140-3 |
| -- | .606 | .079-.083 | 2-448140-2 |
| 3 | .651 | .087 MAX | 1-448140-9 |
| -- | .505 | .079-.083 | 1-448140-8 |
| -- | .617 | .079-.083 | 1-448140-5 |
| -- | .404 | .079-.083 | 1-448140-2 |
| 3 | .536 | .087 MAX | 448140-9 |
| -- | .415 | .079-.083 | 448140-8 |
| -- | .651 | .079-.083 | 448140-6 |
| -- | .536 | .079-.083 | 448140-3 |
| -- | .536 | .079-.083 | 448140-2 |

- 2 COLOR CODE: AS SHOWN IN APPROXIMATE LOCATION SHOWN. THE YELLOW BAND SHALL BE APPROXIMATELY TWICE THE WIDTH OF THE ORANGE BAND.
- 3 ELECTRICAL ENGAGEMENT POINT.
- 4 THIS AREA SOLDER DIPPED.
- 5 MANUFACTURERS LOGO; LACATION & ORIENTATION OPTIONAL.
- 6 SOLDER IS RoHS-COMPLIANT Sn.

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN: C.C. THOMAS 27OCT2009
 CHK: K. THACKSTON 27OCT2009
 APVD: K. THACKSTON 27OCT2009

STE TE Connectivity

NAME: POSTED PIN CONTACT, SIZE 12, ARINC 600

SIZE: A1 CAGE CODE: 448140 DRAWING NO: 100779

SCALE: 12:1 SHEET 1 OF 1 REV U