


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	17	L3	PER ECR-13-018516	02DEC2013	HZ RZ

PART NUMBER	LENGTH (METERS)	
501232-1	25+0.25/-0.0	
501232-2	50+0.5/-0.0	OBSOLETE $\triangle 5$
501232-3	100+1.0/-0.0	
501232-4	1000+10/-0.0	
501232-5	NON SALEABLE PART	
501232-6	500+5.0/-0.0	OBSOLETE
501232-7	NON SALEABLE PART	OBSOLETE $\triangle 5$

- $\triangle 1$. STEP INDEX PLASTIC OPTICAL FIBER
 - 1.1 CORE REFRACTIVE INDEX: 1.49 TYP.
 - 1.2 CLAD REFRACTIVE INDEX: 1.42 TYP
 - 1.3 NUMERICAL APERTURE: 0.46 TYP.
 - 1.4 CORE DIAMETER: 980±60um
 - 1.5 CLAD DIAMETER: 1000±60um
- $\triangle 2$. JACKET:
 - 2.1 MATERIAL: POLYETHYLENE.
 - 2.2 COLOR: BLACK.
3. ATTENUATION AT 650nm AND 25°C:
 - 3.1 TYPICAL: 140dB/km.
 - 3.2 MAX: 150 dB/km.
4. RATINGS:
 - 4.1 OPERATING TEMPERATURE: -40°C TO +85°C.
 - 4.2 STORAGE TEMPERATURE: -40°C TO +85°C.
 - 4.3 MINIMUM BEND RADIUS: 25mm.
 - 4.4 TENSILE STRENGTH: 8kg.
 - 4.5 CABLE WEIGHT: 3.75 kg/km TYP.
- $\triangle 5$ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. BROUGHTON 09SEP05																				
DIMENSIONS: mm		CHK A. BROUGHTON 09SEP05																				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. DARR 09SEP05	NAME CABLE, FIBER OPTIC, 1000um PLASTIC																			
<table border="1"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>-</td></tr> <tr><td>2 PLC</td><td>±</td><td>-</td></tr> <tr><td>3 PLC</td><td>±</td><td>-</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> </table>		0 PLC	±	-	1 PLC	±	-	2 PLC	±	-	3 PLC	±	-	4 PLC	±	-	ANGLES	±	-	PRODUCT SPEC -	SIZE A2	CAGE CODE 00779
0 PLC	±	-																				
1 PLC	±	-																				
2 PLC	±	-																				
3 PLC	±	-																				
4 PLC	±	-																				
ANGLES	±	-																				
MATERIAL -		FINISH -	WEIGHT -	DRAWING NO 501232																		
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1																		
			REV L3	RESTRICTED TO -																		