


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .  
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CE	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED PER NPR	10FEB06	CSV	JD

1. DIMENSIONS IN [ ] ARE IN INCHES
2. 0.5dB MAX INSERTION LOSS
3. 65dB MIN RETURN LOSS
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



25±0.3 [984±12]	2-5492189-5
20±0.3 [787±12]	2-5492189-0
15±0.15 [591±6]	1-5492189-5
10±0.15 [394±6]	1-5492189-0
7±0.08 [275±3]	5492189-7
5±0.08 [197±3]	5492189-5
3±0.05 [118±2]	5492189-3
2±0.05 [79±2]	5492189-2
1±0.05 [39±2]	5492189-1
L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.S.VASU 10 FEB 06	AMP Incorporated Harrisburg, PA 17105-3608													
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN 10 FEB 06														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.DUNCAN 10 FEB 06	NAME CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE LDS, FC/APC TO SC/APC													
<table border="0"> <tr> <td>0 PLC</td> <td>± -</td> </tr> <tr> <td>1 PLC</td> <td>± -</td> </tr> <tr> <td>2 PLC</td> <td>± -</td> </tr> <tr> <td>3 PLC</td> <td>± -</td> </tr> <tr> <td>4 PLC</td> <td>± -</td> </tr> <tr> <td>ANGLES</td> <td>± -</td> </tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC -	RESTRICTED TO -	
0 PLC	± -															
1 PLC	± -															
2 PLC	± -															
3 PLC	± -															
4 PLC	± -															
ANGLES	± -															
MATERIAL -		APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-5492189											
FINISH -		WEIGHT -	SCALE NTS		SHEET 1 OF 1											
CUSTOMER DRAWING			REV A													