

4

3



2


1

THIS DRAWING IS UNPUBLISHED.      RELEASED FOR PUBLICATION


© 2016 Commscope, Inc. Confidential      ©2016. These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose submitted in writing to COMMSCOPE, INC.

REVISIONS					
#	LR	DESCRIPTION	DATE	DWG	APPD
F		REV PER ECN 8000019118	17JAN2017	GG	AS

- ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
-  MATERIAL: COPPER IRON ALLOY, 0.46 [.018] THICK.
-  SPLICE CONNECTOR MARKED WITH "PART NUMBER, UL LOGO, CSA LOGO AND 10/12 AWG" ON FARSIDE.
- APPLICATION: UNDERCARPET POWER CABLING; SEE INSTRUCTION SHEET 408-3128.



UNDERCARPET APPLICATION	553454-1 PART NO.
-------------------------	-------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG G GARRETT 24MAR97	COMMSCOPE, INC.	
		CHK G GARRETT 24MAR97		
		APVD J KILPATRICK 24MAR97	NAME	
DIMENSIONS: MM [INCHES]		PRODUCT SPEC	CONNECTOR, SPLICE, 10/12 AWG	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	-	
0 PLC ± -		WEIGHT	-	
1 PLC ± -		SIZE	A2	
2 PLC ± -		SCALE	4:1	
3 PLC ± -		RESTRICTED TO	-	
4 PLC ± -		REV	F	
ANGLES ± -		C=553454		
MATERIAL 	FINISH -	CUSTOMER DRAWING		
		SCALE	1 OF 1	
		SHEET	REV	