





THIS DRAWING IS UNPUBLISHED.      RELEASED FOR PUBLICATION      - , 18SEP2008

© 2018 Commscope, Inc. Confidential      ©2018. These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.

REVISIONS					
#	LR	DESCRIPTION	DATE	DWG	APPD
F		REV PER ECN 8000019118	17JAN2017	GG	AS

- ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
-  MATERIAL: COPPER IRON ALLOY, 4.57 [.018] THICK.
-  TAP CONNECTOR MARKED WITH  10/12 AWG LOCATED ON FAR SIDE.
- APPLICATION: UNDERCARPET POWER CABLING; SEE INSTRUCTION SHEET 408-3128.



553455-1  
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG L HALL 18SEP2008	COMMSCOPE, INC.																			
DIMENSIONS: MM [INCHES]		CHK S JONES 18SEP2008	ASSEMBLY, CONNECTOR, TAP, 10/12 AWG																			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPD S JONES 18SEP2008	PRODUCT SPEC	RESTRICTED TO																		
<table border="1"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>-</td></tr> <tr><td>2 PLC</td><td>±</td><td>-</td></tr> <tr><td>3 PLC</td><td>±</td><td>-</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> </table>		0 PLC	±	-	1 PLC	±	-	2 PLC	±	-	3 PLC	±	-	4 PLC	±	-	ANGLES	±	-	APPLICATION SPEC	SIZE A2	DRAWING NO C=553455
0 PLC	±	-																				
1 PLC	±	-																				
2 PLC	±	-																				
3 PLC	±	-																				
4 PLC	±	-																				
ANGLES	±	-																				
MATERIAL -	FINISH -	WEIGHT -	SCALE 2:1	SHEET 1 of 1																		
CUSTOMER DRAWING			REV F																			