



DESCRIPTION	MATERIAL	FINISH
GROMMET	FLUOROSILICONE MPS #10149	COLOR: RED
SPLICE ASSEMBLY HOUSING	EPOXY	COLOR: BLACK
CONTACT FEMALE SOCKET	BERYLLIUM COPPER PER ASTM-B194	GOLD PLATE ASTM-B-488
CLIP CONTACT RETAINING	BERYLLIUM COPPER PER ASTM-B194 OR STAINLESS STEEL PER QQ-S-766	NONE
SHRINK TUBE	PER MIL-1-23053/8	COLOR TRANSPARENT
DIODE	1N3981	NONE

P	LTR	DESCRIPTION	DATE	OWN	APVD
B		REVISED PER ECO-20-009603	5-19-21	CT	DC



SCHEMATIC



- 1 MARK SPLICE IDENTIFICATION "TE" PER TEC-202-36, AND TE PART NO. AND DATE CODE .060 MINIMUM HIGH CHARACTERS PER 115-10002-2
- 2 MARK WIRE SPLICE BUSSING ARRANGEMENT BOTH ENDS AS SHOWN.

591889-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN C.C. THOMAS 8-30-12		
DIMENSIONS: INCHES		CHK D. EABY 8-30-12		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. EABY 8-30-12	NAME WIRE SPLICE ASSY DOUBLE W/ DIODE SIZE 20, TJ	
0 PLC ± -		PRODUCT SPEC	SIZE	CAGE CODE
1 PLC ± -		APPLICATION SPEC	A200779	DRAWING NO
2 PLC ± -			C=591889	RESTRICTED TO
3 PLC ± -				
4 PLC ± -				
ANGLES ± -		WEIGHT 0.000000	SCALE 4:1	SHEET 1 OF 1
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING	REV B	