



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REV PER ECR 07-027142	13NOV07	JR	TM
	N1	REVISED PER ECO-17-016703	03APR2018	RS	DR
	N2	REVISED PER ECO-18-011826	26JUL2018	RS	DR



1 TUBING MATERIAL; CROSS-LINKED POLYMER WITH MELT LINER; COLOR, YELLOW; BLACK INK LEGEND 1/16 MIN; HEIGHT; ONE FULL APPEARANCE MIN.

2 TEMP RATING -65°F TO 257°F [-55°C TO 125°C ]

3 NOTE DELETED

4 SHIPPING WEIGHT .007 LBS EACH

5 VOLTAGE RATING: 600 V MAX ( 1000 V MAX FIXTURES & SIGNS )

6 MATERIAL & FINISH ; BODY - COPPER, TIN PLATED SLEEVE - NYLON

7 NOTE DELETED

LOOSE PIECE	6.350 [.250]	2.921 [.115]	1000	603504-3
SMALL PACK	6.350 [.250]	2.921 [.115]	50/BOX	603504-2
PACKAGE TYPE	EXPANDED I.D. MIN	RECOVERED I.D. MAX	QTY	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 24JUN04	TE Connectivity Ltd.			
DIMENSIONS: mm [INCHES]		CHK T MICHIELUTTI 24JUN04				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHIELUTTI 24JUN04	NAME			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC	PRE-INSULATED SEALED SPLICE WIRE SIZE: 12-10 AWG			
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
FINISH		WEIGHT	A3	00779	C-603504	-
		CUSTOMER DRAWING		SCALE	SHEET	REV
				1:1	1 OF 1	N2