



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	0	RELEASED	17-JAN-00	KW	JS
	A	REDRAWN PER ECO-17-002880	31AUG2017	BDA	DR

- 1 ACCOMODATES CABLE TIES WITH TENSILE VALUE OF 133.44 NEWTONS [30 LBS] MAXIMUM.
- 2 AS SHOWN - PACKAGED 100 PER SEALED POLY BAG WITH LABEL TO CONTAIN AMP P/N DESCRIPTION, QUANTITY, DATE CODE, AND U.L. RECOGNITION MARK.



608802-1
PART NUMBER

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. © COPYRIGHT - TE Connectivity

DIMENSIONS: mm [INCHES]	DWN K. WHITAKER 17-JAN-2000	MATERIAL NYLON, WHITE	FINISH -		
	CHK J. SCHLUNZ 17-JAN-2000				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.51 [0.02] 3 PLC ± - 4 PLC ± - ANGLES ± 0° 30'	APVD J. SCHLUNZ 17-JAN-2000			NAME 4 WAY CABLE TIE MOUNT 2 #4 SCREW HOLES, W/ADHESIVE	
	PRODUCT SPEC -	SIZE A4	CAGE CODE 00779	DRAWING NO C=608802	RESTRICTED TO -
	APPLICATION SPEC -	WEIGHT		CUSTOMER DRAWING	SCALE 3:1
		SHEET 1 OF 1		REV A	