



THIS DRAWING IS A CONTROLLED DOCUMENT
 6828260

USED ON



Left Side

Connector(s): MT-RJ SECURE (No Pins)
 Mode: MM
 Housing Color: Violet
 Geom. Spec: 115-1215



Fiber Path

Fiber A - - B
 Fiber B - - A

Notes:

- 1 IL tested at 1300nm.
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 3 Label 2 will not be present on any cable assembly less than 5 meters long.
- 4 Includes dust caps (not shown on print).

Right Side

Connector(s): SC-Duplex
 Mode: MM
 Housing Color: Beige
 Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

LOC	CE
DIST	16

A	Rev Per EC#	RELEASE	5/28/2009	-	JB		
P	LTR	REVISION RECORD	DATE	DN	APVD		

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	0 PLC ± .
	1 PLC ± .
	2 PLC ± .
	3 PLC ± .
	4 PLC ± .

Restricted To:

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
CHK	James Barry		
APVD	James Barry	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME	FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 6828260	1 of 3
			REV
			A

