


© TE Connectivity. All Rights Reserved.


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
K1		REVISED PER ECN-22-190736	25NOV2022	KH SZ




- NOTE DELTA
- MOLD PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL 94V-0 RATED. COLOR: BLACK. CONTACT MASS: .000100 MIN. SHELLS: STAINLESS STEEL.
- CONTACT FLASH FROM LENGTH OF .000100 MIN FROM MATING END, .000100 MIN TIN-LEAD ON OPPOSITE END, ALL OVER .000100 MIN NICKEL.
- CONTACTS: GOLD PLATED FOR A LENGTH OF .150 FROM MATING END, .000030 MIN THICKNESS. GOLD IN MATED AREA, .000100 MIN TIN-LEAD ON OPPOSITE END, ALL OVER .000050 MIN NICKEL.
- CONTACTS: .000200 MIN TIN OVER .000100 MIN COPPER.

GROUNDING INDENTS


MATING FACE



"AMP", PART NO. & DATE CODE, STAMPED IN AREA INDICATED, ON FAR SIDE



P.C. BOARD MOUNTING DIMENSIONS



SUPSD BY 745411-1	3	.188	745411-8
SUPSD BY 745411-1	4	.188	745411-7
OBSOLETE	3	.651	745411-6
OBSOLETE	4	.651	745411-5
OBSOLETE	3	.427	745411-4
OBSOLETE	4	.427	745411-3
SUPSD BY 745411-1	3	.125	745411-2
	4	.125	745411-1
CONTACT FINISH	DIMENSION A	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J. GERACE	10-29-83	<p>TE Connectivity</p>
DIMENSIONS: INCHES		CHK	J. GERACE	10-29-83	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	B. TAYLOR	1-4-84	
0 PLC ± - 1 PLC ± - 2 PLC ± .005 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC	108-40025		
MATERIAL		APPLICATION SPEC	114-40013		NAME
FINISH		WEIGHT	0.000000		PLUG ASSEMBLY, SIZE 2, 15 POS, VERTICAL, W/ GROUNDING INDENTS, AMPLIMITE
SHELLS: 5		SCALE	A2 00779		DRAWING NO
CONTACTS: SEE TABLE		CUSTOMER DRAWING	C=745411		RESTRICTED TO
		SCALE	NTS		SHEET
		SHEET	1 OF 1		REV
		REV	K1		