

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED(FC00-0115-03)	28.AUG.'03	HS	CS
	A2	REVISED(ECR-18-002810)	26.FEB'18	CH	YJ
	A3	REVISED(ECR-19-009528)	17.JUN'19	JS	YJ
	A4	REVISED(ECR-19-009681)	20.MAY'19	YH	YJ

35.5±0.3
(34.9)
(19.5)
(3.5)

-A-

16.6±0.3
12.6
5.2 3.4
1.26 (A2)
2.3
6.5
15
23.5
39.6±0.3
23
26.5
30
34.8

B B
C C

SECTION B-B
LANCE DETAIL

(11.4) (10.5)
(16.6)

SECTION C-C

NOTE

- MUST BE KEPT BETWEEN $\square A$ AND 2.
- TO BE MATED WITH REC HSG SMOOTHLY
- APPLIED TAB CONTACT PART NUMBERS
- APPLIDE REC HSG P/N; 85109
.070 SERIES : 173633, 173645
.250 SERIES : 170340, 170341, 170349

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 <XX<10 ± 0.2 10<XX<30 ± 0.25 30<XX ± 0.3 ANGLES ± 3°
MATERIAL SEE TABLE	FINISH

85110-2	PLUG HSG	PBT	BLACK
85110-1	PLUG HSG	PBT	WHITE
PART NUMBER	DESCRIPTION	MATERIAL	COLOR
STE TE Connectivity			
NAME .070/.250 HYBRID 11P CAP HSG			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C- 8 5 1 1 0	
CUSTOMER DRAWING		SCALE 2 : 1	SHEET 1 OF 1 REV A4

1470-19 (3/13)