


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
J		REV PER 0010-0659-96	11DEC96	-	JS
K		REVISED PER ECO-18-000976	24MAY2018	RS	JO



- ① CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF .100 TOLERANCES ARE NON-CUMULATIVE.
- 2. USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
- ③ AMP LOGO MOLDED IN TEXTURED AREA AS SHOWN.

OBSOLETE	2.405	1.100	1.200	24	2-86427-2
OBSOLETE	3.005	1.400	1.500	30	2-86427-0
OBSOLETE	.905	.400	.400	9	1-86427-7
SUPERSEDED BY 1-86426-6	5.005	2.400	2.500	50	1-86427-6
OBSOLETE	3.005	1.700	1.800	36	1-86427-5
OBSOLETE	1.605	.700	.800	16	1-86427-4
OBSOLETE	1.205	.500	.600	12	1-86427-3
OBSOLETE	1.805	.800	.900	18	1-86427-2
	.305	.100	.100	3	1-86427-1
OBSOLETE	.405	.100	.200	4	1-86427-0
OBSOLETE	.605	.200	.300	6	86427-9
SUPERSEDED BY 86426-7	.505	.200	.200	5	86427-7
OBSOLETE	1.505	.700	.700	15	86427-6
OBSOLETE	.805	.300	.400	8	86427-5
OBSOLETE	1.405	.600	.700	14	86427-4
OBSOLETE	2.005	.900	1.000	20	86427-3
OBSOLETE	1.005	.400	.500	10	86427-2
OBSOLETE	.705	.300	.300	7	86427-1

C	B	A	NO OF POS	PART NUMBER
---	---	---	-----------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	1-25-90	TE Connectivity Ltd.			
CHK	10-5-93				
APVD	1-27-90	CONNECTOR HOUSING, CRIMP SNAP-IN MOD IV, SINGLE ROW, .100 CENTERS			
NAME					
PRODUCT SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
APPLICATION SPEC		A2	00779	C-86427	-
MATERIAL	GLASS FILLED NYLON COLOR-BLACK	WEIGHT	CUSTOMER DRAWING		
DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		SCALE	4:1	SHEET	1 of 1
		REV	K		