



SECTION Y-Y
LOADED HSG
SCALE 4:1
(FOR REF ONLY)

- ① HOUSING WILL ACCOMODATE FLEXIBLE FLAT CABLE .050 OR .062 WIDE CONDUCTORS (CABLE .015 MAX THK) AND/OR #22-32 AWG WIRE WITH INSULATION RANGE OF .045 TO .069 DIA.
- ② MOLDED "AMP" TRADEMARK, IN THIS AREA
- ③ PART NO. AND DATE CODE TO BE LASER MARKED
- ④ DETENTS: 6,8,10,12 & 18 POSN,(1) DETENT LOCATED AS FOLLOWS:
6 & 8 POSN- ϕ OF THRID CIRCUIT FROM RIGHT
10 & 12 POSN- ϕ OF FOURTH CIRCUIT FROM RIGHT
18 POSN- ϕ OF SIXTH CIRCUIT FROM RIGHT
20 POSN & ABOVE- (2) DETENTS LOCATED AS SHOWN
- ⑤ CAVITY IDENT NO. TO BE LASER MARKED (SEE TABLE)
- ⑥ INDICATES POSITION 1, SURFACE TEXTURE CONTRAST'S WITH REST OF HOUSING
- ⑦ THIS HOUSING WILL MATE WITH FFC PIN HOUSING
- ⑧ OBSOLETE PART NUMBER
- ⑨ SUPERSEDED BY AS MOLDED PART NUMBER.
- ⑩ GLASS-FILLED NYLON, BLACK, UL V-0.
- ⑪ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

⑧ 4-88179-1	12-15-22	2-5-10	1.350	1.234	1.140	22	⑧ 4-88179-2
⑧ 3-88179-9			.650	.534	.440	8	⑧ 4-88179-0
⑧ 3-88179-7	16-20-25-30	2-5-10-14	1.750	1.634	1.540	30	⑧ 3-88179-8
⑨ 3-88179-5	18-25-30-34	2-5-10-16	1.950	1.834	1.740	34	⑧ 3-88179-6
① 3-88179-3	7-12	2-5	.850	.734	.640	12	⑧ 3-88179-4
⑧ 3-88179-1	4-6	2	.550	.434	.340	6	⑧ 3-88179-2
⑧ 2-88179-9	6-10	2-4	.750	.634	.540	10	⑧ 3-88179-0
⑧ 2-88179-7			3.750	3.634	3.540	70	⑧ 2-88179-8
⑧ 2-88179-5			3.150	3.034	2.940	58	⑧ 2-88179-6
⑧ 2-88179-3	23-25-30-35-40-44	2-5-10-15-20-21	2.450	2.334	2.240	44	⑧ 2-88179-4
⑧ 2-88179-1	21-25-30-35-40	2-5-10-15-19	2.250	2.134	2.040	40	⑧ 2-88179-2
⑧ 1-88179-9	19-25-30-36	2-5-10-17	2.050	1.934	1.840	36	① 2-88179-0
⑧ 1-88179-7			1.650	1.534	1.440	28	⑧ 1-88179-8
⑧ 1-88179-5	14-20-26	2-5-12	1.550	1.434	1.340	26	① 1-88179-6
① 1-88179-3	13-20-24	2-5-11	1.450	1.334	1.240	24	⑧ 1-88179-4
① 1-88179-1	26-30-35-40-45-50	2-5-10-15-20-24	2.750	2.634	2.540	50	⑧ 1-88179-2
① 88179-9	10-15-18	2-5-8	1.150	1.034	.940	18	⑧ 1-88179-0
⑧ 88179-7	34-40-45-50-55-60-66	2-5-10-15-20-25-32	3.550	3.434	3.340	66	① 88179-8
⑧ 88179-3	20-25-30-35-38	2-5-10-15-18	2.150	2.034	1.940	38	⑧ 88179-6
① 88179-2	11-15-20	2-5-9	1.250	1.134	1.040	20	⑧ 88179-5
⑧ 88179-1			3.250	3.134	3.040	60	⑧ 88179-4

LASER MARKED PART NUMBER	FAR SIDE CAVITY POSN NO.	NEAR SIDE STAMPED	C	B	A	NO OF POS'N	AS MOLDED PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT. DATE 11/07/88 KATE HELM 3-6-89 CHK D.L.ROCKER APVD - NAME DIMENSIONS: INCHES TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - MATERIAL ⑩ FINISH - WEIGHT - SIZE A1 CAGE CODE 00779 DRAWING NO. 88179 CUSTOMER DRAWING SCALE 3:1 SHEET 1 OF 1 REV AR3							