

DRAWING NO: FGD0550-0595-4L-C


THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: FGD0550-0595-4L SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
3/2.75	SC/GZ	5.93	LEFT HAND




TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FGD0550-0595-4L
DESCRIPTION: FULL-TENSION GALVANISED STEEL DEADEND
MATERIAL: HEAVILY GALVANISED STEEL WIRE
NUMBER OF RODS: 4
ROD DIAMETER: 2.03mm
OVERAL LENGTH: 655mm
END FINISH: CHAMFERED
FITTING LAY DIRECTION: LEFT HAND
COLOUR CODED: WHITE

PRODUCT LABEL



BOX LABEL



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.

LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5% UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°	TCPN -	PART Alias UTX/DUL FGD0550-0595-4L	TITLE FULL-TENSION GALVANISED STEEL DEADEND (FGD) FITTING COND. RANGE: Ø5.50-Ø5.95 LEFT HAND LAY 3/2.75 SC/GZ					
DIST	—	I	NEW RELEASE	13-05-2013	RN	AT	MATERIAL DESC HEAVILY GALVANISED STEEL WIRE	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	Cat No FGD0550-0595-4L	DRAWN RN	DATE 13-05-2013	TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia		
POS	REV	REVISION RECORD		DATE	DWN	APVD	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO FGD0550-0595-4L-C	SHEET 1	OF 1	REV 1

Format: generic_m03.au.r1.fm 4

Template: tec_generic_a3.metric.au.r1.drw 3

Dwg No from P1 Mod Fam Tbl: 2 >AUXXXXX