


DRAWING NO: FLD0550-0595-4L-C
THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: FLD0550-0595-4L SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
3/2.75	SC/AC	5.93	LEFT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FLD0550-0595-4L
 DESCRIPTION: FULL-TENSION ALUMINIUM CLAD STEEL DEADEND
 MATERIAL: ALUMINIUM CLAD STEEL WIRE
 NUMBER OF RODS: 4
 ROD DIAMETER: 2.34mm
 OVERAL LENGTH: 630mm
 END FINISH: CHAMFERED
 FITTING LAY DIRECTION: LEFT HAND
 COLOUR CODED: GREEN / WHITE

BOX LABEL

P/N: FLD0550-0595-4L
 ID:
 DESCRIPTION:
FULL-TENSION AL-CLAD STEEL DEADEND
3/2.75 SC/AC

RANGE: 5.50 - 5.95
 COLOUR-CODE: **GREEN / WHITE**
 QTY: 50 WEIGHT: BATCH:

PRODUCT LABEL

FLD0550-0595-4L
3/2.75 SC/AC

WEIGHT: 0.19kg
 BATCH NO:
 MONTH/YEAR:

LOC	DIST	POS	REV	REVISION RECORD	DATE	DWN	APVD	MATERIAL NO	MATL SPEC/STD/DRG NO	PROCESS SPEC HEAT TREAT/PLATING NO	SIZE	PROJECTION	SCALE	DRAWING NO	SHEET	OF	REV			
			I	NEW RELEASE	13-05-2013	RN	AT				A3	3RD ANGLE	NTS	FLD0550-0595-4L-C	1	1	1			
								IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE		IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ± 0.5 mm. DIMENSIONS UP TO 30mm: ± 1.5 mm. DIMENSIONS OVER 30mm: $\pm 5\%$. UP TO A MAX OF ± 5 mm. ANGULAR DIMENSIONS: $\pm 5^\circ$.		TCPN -		TITLE FULL-TENSION ALUMINIUM-CLAD STEEL DEADEND (FLD) FITTING COND. RANGE: $\varnothing 5.50 - \varnothing 5.95$ 3/2.75 SC/AC						
								MATERIAL DESC ALUMINIUM CLAD STEEL WIRE		PART Alias UTX/DUL FLD0550-0595-4L		Cat No FLD0550-0595-4L		DRAWN RN		DATE 13-05-2013		TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia		
								CHECKED MN		APPROVED AT		SHEET 1		OF 1		REV 1				
								Format: generic_m03_ou.r1.frm		4		Template: tec_generic_a3_metric_ou.r1.drw		3		Dwg No from P1 Mod Fam Tbl: 2		>AUXXXXX		

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.