


NOTES

1. PART NO. BREAKDOWN EXAMPLE:



2. CONTACT SERVICE RATING @ STANDARD TEMPERATURE AND PRESSURE:

- CONTINUOUS CURRENT = 300A.


3. TEMPERATURE RATING -55°C TO +120°C.

(THE UPPER LIMIT IS THE MAXIMUM AMBIENT TEMPERATURE RATING WHEN CONNECTOR IS IN SERVICE AT MAXIMUM CURRENT).

A	55886	NDL	JAK	JAK	IKG	22/05/08
ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. MARKTG.	DATE

MATERIAL	
HEAT TREATMENT & FINISH	
PACKAGING	
APPROVED IED	

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH LTD. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH LTD.

GENERAL TOLERANCES UNLESS OTHERWISE STATED.
±0.4mm ON WHOLE NUMBERS
±0.2mm ON ONE PLACE DECIMALS
±0.1mm ON TWO PLACE DECIMALS
±1/2° ON ANGLES
±0.05mm ON DRILLED HOLES
ALL DIAMETERS  0.10
REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.
DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED



DEUTSCH
A STEP AHEAD IN TECHNOLOGY LTD

ST LEONARDS ON SEA, EAST SUSSEX, TN38 9RF
TEL. +44 (0)1424 852721

TITLE
ASHD PLUG. POWER CONNECTOR
SIZE 23 SHELL
SIZE 00 300A CONTACT

DRAWING NUMBER
610233-ASHD-ENV