

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2016

© COPYRIGHT 2002 BY TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
| C | | REVISED PER PCN-24-210155 | 22APR2024 | PS | CB |
| | | | | | |
| | | | | | |

GROMMET

HOUSING

FRONT SEAL

WEDGE LOCK

SNAP CAP

3D VIEW

4 RESISTOR CHARACTERISTICS: 120 OHMS \pm 10 PERCENT,
.4 WATTS MINIMUM INSERTED INTO THE CAVITIES A AND B.

3 THIS CONNECTOR CAN PASS THRU A ONE INCH [25.44] HOLE.

2 MATERIAL: HOUSING/CAP: PA66 GF15 (BLACK)
GROMMET: VMQ (RED-ORANGE)
FRONT SEAL: VMQ (RED-ORANGE)
WEDGE LOCK: PBT GF30 (BLUE)
SOCKET TERMINAL: COPPER ALLOY; GOLD PLATED

1 THIS PLUG MATES WITH THE DT04-3P-XXXX RECEPTACLE.
(XXXX = J1939 MODIFICATIONS.)
CONSULT FACTORY FOR MODIFICATIONS.
SECONDARY WEDGE LOCK W3S-1939-P012 IS KEYED AND INCLUDED
TO PREVENT MISMATING AND MAY MATE WITH ALL 3 WAY DT
SERIES RECEPTACLES.

NOTES:

| TE INTERNAL PN | DEUTSCH PN | PN REV |
|----------------|--------------|--------|
| DT06-3S-EPI0 | DT06-3S-EPI0 | C |

| | | | | | |
|--|--|-----------------------------------|---|--------------------|----------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN X. SANCHEZ 11NOV2002 |  TE Connectivity | | |
| DIMENSIONS: in [mm] | | CHK A. ROLINSKI 21NOV2002 | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD S. BEARD 02DEC2002 | NAME 3 WAY PLUG, D.T. SERIES (TERMINATING PLUG) -EPI0 MOD | | |
| 0 PLC \pm 1 PLC \pm 2 PLC \pm 3 PLC \pm 4 PLC \pm ANGLES \pm FINISH $\pm 1^\circ$ | | PRODUCT SPEC 108-151009 | RESTRICTED TO - | | |
| MATERIAL | | APPLICATION SPEC 0425-017-0000 | SIZE A3 | CAGE CODE 4AFU8 | DRAWING NO DT06-3S-EPI0 |
|   | | WEIGHT 9.00g | SCALE 3:1 | | |
| | | CUSTOMER DRAWING | SHEET 1 OF 1 | | |
| | | | REV C | | |

1470-19 (3/13)