



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION. ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A1	NEW DRAWING	09DEC2016	GK KM

PRESENTATION




PRINTING/DIMENSION



RADIUS = 4 x .060 inch [4 x 1.5 mm]

LABEL BUILD DETAIL



All dimensions in Inches [mm]

MATERIAL	THERMAL TRANSFER PRINTABLE PAPER
ADHESIVE TYPE	ACRYLIC PERMANENT
NOM THICKNESS	0.07 MM [.003 INCH]
BACKGROUND COLOURS	WHITE
WOUND	OUTSIDE WOUND

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GOPALAKRISHNA HV 09DEC2016		
		CHK K. MUNZ 09DEC2016		
		APVD K. MUNZ 09DEC2016	NAME EP ECONOMY PAPER LABEL	
		PRODUCT SPEC	-	
		APPLICATION SPEC	-	
		WEIGHT	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=EP-318097-10-9	
			RESTRICTED TO	REV A1
			SCALE NTS	SHEET 1 of 1

TOLERANCES	INCH [mm]
LABEL HEIGHT	±.018 [0.3]
LABEL WIDTH	±.018 [0.3]
WEB WIDTH	±.039 [1.0]
VERTICAL REPEAT	±.039 [1.0]
HORIZONTAL REPEAT	±.039 [1.0]
PRINT POSITIONING	±.039 [1.0]
*NON ACCUMULATING	

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES [mm]	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH
-	-