



REV. A  
DCO 300860

TOLERANCES  $\pm .010$ " - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C	
RESISTANCE	320 OHMS $\pm 10\%$
NOMINAL VOLTAGE	28 VDC
MUST OPERATE	13.5 VDC MAX.
MUST RELEASE	5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:	
VIBRATION	33 Hz TO 3000 Hz @ 30 g's
SHOCK	200 g's 6 MS. DURATION
TEMPERATURE	-70 °C TO +125 °C

NOTES: OPERATE, RELEASE 10 MS MAX.  
CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET



BLUE BEAD → + X1

TERMINAL VIEW

CONTACT RATING:	
	25 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE
	50,000 OPERATIONS

DR. B.D. 21MAY2008 CK. J.M.B. 5/21/08

**Tyco Electronics**

©COPYRIGHT 2005  
TYCO ELECTRONICS CORPORATION  
ALL INTERNATIONAL RIGHTS RESERVED

CUST. CATALOG ITEM	TE NUMBER
CUST. NO. ---- REV. ----	6-1617748-0

CII PART NUMBER  
FCA-125-AY3