



REV. B  
DCO 300860

TOLERANCES  $\pm .010$ " - UNLESS  
OTHERWISE SPECIFIED

COIL: @ 25°C	
RESISTANCE	20 OHMS $\pm 10\%$
NOMINAL VOLTAGE	6 VDC
MUST OPERATE	3.30 VDC MAX.
MUST RELEASE	1.80 VDC MAX., 0.40 VDC MIN.

ENVIRONMENT:	
VIBRATION	33 Hz TO 3000 Hz @ 30 g's
SHOCK	200 g's 6 MS. DURATION
TEMPERATURE	-70 °C TO +125 °C

NOTES: OPERATE, RELEASE 10 MS MAX.  
CONTACT BOUNCE 1 MS MAX.

### CUSTOMER DATA SHEET



BLUE BEAD → + X1

TERMINAL VIEW

CONTACT RATING: \_\_\_\_\_  
25 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE  
50,000 OPERATIONS

DR. B.D. 21MAY2008 CK. J.M.B. 5/21/08

**Tyco Electronics**

©COPYRIGHT 2005  
TYCO ELECTRONICS CORPORATION  
ALL INTERNATIONAL RIGHTS RESERVED

CUST. \_\_\_\_\_ CATALOG ITEM \_\_\_\_\_  
CUST. NO. \_\_\_\_\_ REV. \_\_\_\_\_

TE NUMBER  
6-1617748-4

CII PART NUMBER

FCA-125-BY1