

MSD INC.

ENGINEERING DATA SHEET

RELAY TYPE: FCB-205-HX3	COMPUTER PART No.: 9347550	TEST PROCEDURE MSDP-791
CUSTOMER/SPECIFICATION: CATALOG ITEM		REV NONE

±10% TEST REQUIREMENTS

COIL RES.: 500 OHMS OPERATE TIME: 5 mS MAX RELEASE TIME: 5 mS MAX

CONTACT MAKE BOUNCE: 1 mS MAX N.O. BREAK BOUNCE: N/A

CONTACT STABILIZATION TIME: N/A RATED COIL VOLTAGE: 28 Vdc

CONTACT RES.: MFG TEST: .040 OHMS @ 10mA - 6Vdc FINAL TEST: .050 OHMS @ 10mA - 6Vdc

CONTACT VOLTAGE DROP: FINAL TEST: .100 V MAX @ 5A - 6Vdc


HI-POT: 1000 Vrms ALL POINTS

INSULATION RESISTANCE: 100 MEGOHMS MIN. @ 500 Vdc

VIBRATION: N/A

SEAL TEST: 1 X 10⁻⁸ MAX LEAK RATE COIL TRANSIENT SUPPRESSION: N/A

OTHER: _____



Prepared By: Date		Approved By: Date	
LFS WYNNE 3-20-96		<i>[Signature]</i> 3-21-96	
Rev	ECN No.	Date	
B	97-248	12-29-97	

SPECIAL INSTRUCTIONS