


REV. B
DCO 300825

TOLERANCES $\pm .010$ " - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C
 RESISTANCE _____ 400 OHMS $\pm 10\%$
 NOMINAL VOLTAGE _____ 28 VDC
 MUST OPERATE _____ 13.5 VDC MAX.
 MUST RELEASE _____ 5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:
 VIBRATION _____ 57 Hz TO _____ 3000 Hz @ _____ 20 g's
 SHOCK _____ 100 g's _____ 6 MS. DURATION
 TEMPERATURE _____ -70 °C TO _____ +125 °C

CUSTOMER DATA SHEET



CONTACT RATING: _____ LOW LEVEL
 5 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE
 100,000 OPERATIONS

NOTES: OPERATE, RELEASE 6 MS MAX.
 CONTACT STABILIZATION 2.5 MS MAX.
 CONTACT BOUNCE 1 MS MAX.

DR. B.D. 30APR2008 CK. 5/9/08 J.M.B.

Tyco Electronics ©COPYRIGHT 2005
 TYCO ELECTRONICS CORPORATION
 ALL INTERNATIONAL RIGHTS RESERVED

CUST. _____ M83536/5-024M
 CUST. NO. _____ REV. ---

TE NUMBER
 7-1617760-0

CII PART NUMBER
 FCB-405-0524M