



MSD INC.

ENGINEERING DATA SHEET

RELAY TYPE: FCB-405-BZ2 COMPUTER PART No.: 9364536 TEST PROCEDURE  
 CUSTOMER/SPECIFICATION: CATALOG ITEM REV N/A MSDP-791

TEST REQUIREMENTS

COIL RES.: 78 <sup>±10%</sup> OHMS OPERATE TIME: 6ms MAX RELEASE TIME: 6ms MAX  
 CONTACT MAKE BOUNCE: 1ms MAX N.O. BREAK BOUNCE: N/A  
 CONTACT STABILIZATION TIME: N/A RATED COIL VOLTAGE: 12Vdc  
 CONTACT RES.: MFG TEST: .040 OHMS @ 10mA - 6Vdc FINAL TEST: .050 OHMS @ 10mA - 6Vdc  
 CONTACT VOLTAGE DROP: FINAL TEST: .100V MAX @ 5A - 6Vdc  
 HI-POT: 1000 Vrms ALL POINTS  
 INSULATION RESISTANCE: 100 MEGOHMS MIN @ 500 Vdc  
 VIBRATION: N/A  
 SEAL TEST: 1 X 10<sup>-8</sup> MAX LEAK RATE COIL TRANSIENT SUPPRESSION: N/A  
 OTHER: \_\_\_\_\_



Prepared By: Date		Approved By: Date	
LES WYNNE 5-13-96		<i>J. Looney</i> 5-14-96	
Rev	ECN No.	Date	
A	96-065	5-13-96	

SPECIAL INSTRUCTIONS