


COIL: @ 25° C	
RESISTANCE	200 OHMS ± 10%
NOMINAL VOLTAGE	12.6 VDC
MUST OPERATE	6.8 VDC
MUST RELEASE	.74 VDC

ENVIRONMENT:	
VIBRATION	10 CPS TO 2000 CPS @ 20 g's
SHOCK	100 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES: OPERATE & RELEASE TIME 5 MS MAX.
CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 3 AMPS
RESISTIVE 28 VDC 100,000 OPERATIONS

DR. R.B. 5/25/94 CK 5/25/94 GMB



CUST. C.I.I. STD.
CUST. NO.

TYPE 'FW' RELAY

FW1109D00