


COIL: @ 25°C
 RESISTANCE 1130 OHMS ± 10%
 NOMINAL VOLTAGE 18.0 VDC
 MUST OPERATE 10.5 VDC
 MUST RELEASE 6.0 VDC MAX, 0.91 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.
RELEASE TIME 2.0 MS MAX.
CONTACT STABILIZATION TIME 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/2/98 *ES* ~~3/2/98~~ *3/2/98*

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. GPL
 CUST. NO. M39016/7-021P

TYPE "J1MA" RELAY

J1MAW-18XP