

SENSOR SOLUTIONS

KPSI DIGITAL LEVEL TRANSDUCERS

LEVEL TRANSDUCERS—DIGITAL

	Model	Accuracy	Level Range	Diameter	Body Material Options	Nose Cap Options	Electrical Connection Options	Cable Options	List Price
	351	±0.01 Ft H ₂ O	0-50 Ft H ₂ O	0.75"	316 SS or Titanium	Ported or Removable Ported	Overmold, Gland or Removable	Poly or ETFE	SS \$995 Ti \$1,120
	353	±0.10% TEB	0-230 Ft H ₂ O	0.75"	316 SS or Titanium	Ported or Removable	Overmold, Gland or Removable	Poly or ETFE	SS \$645 Ti \$770
	355	±0.05% TEB	0-230 Ft H ₂ O	0.75"	316 SS or Titanium	Ported or Removable Ported	Overmold, Gland or Removable	Poly or ETFE	SS \$795 Ti \$920
	500	±0.05% TEB	0-230 Ft H ₂ O	1.0"	316 SS or Titanium	Open Face, Ported, Piezometer, ¼" NPT or ½" NPT	Overmold, Gland or Removable	Poly or ETFE	SS \$795 Ti \$920
	501	±0.01 Ft H ₂ O meets USGS OSW Spec	0-50 Ft H ₂ O	1.0"	316 SS or Titanium	Open Face, Ported, Piezometer, ¼" NPT or ½" NPT	Overmold, Gland or Removable	Poly or ETFE	SS \$995 Ti \$1,120
	600	±0.05% TEB	0-230 Ft H ₂ O	1.0"	316 SS	Open-Face or ¼ -18 NPT Male	Overmold, Gland or Removable	Poly or ETFE	SS \$995
	601	±0.01 Ft H ₂ O	0-69 Ft H ₂ O	1.0"	316 SS	Open-Face or ¼ -18 NPT Male	Overmold, Gland or Removable	Poly or ETFE	SS \$1295

ACCESSORIES AND OPTIONS

Cabling



Armored Cable

Details

Cable Jacket Material:

- Polyurethane
- ETFE



859 Removable Cable

KPSI 350 and 500 Series Options:

- Poly, ETFE or Armored
- 316 SS or Titanium
- Configurable Lengths

Nose Caps

Details



1" Nose Cap

Traditional Nose Cap



0.75" Nose Cap

KPSI 350 Series Option

Accessories & Options

Details



811 Stainless Steel Vent Filter

Lightning Protection Option:

- Transducer Only (no external surge protector)
- Two Year Warranty = No Charge
- Lifetime Warranty = \$95

FOR MORE INFORMATION CONTACT:

TE Connectivity
 1.800.745.8008
customercare.hmpt@te.com
te.com/sensors
levelandpressure.com