

COIL: 12.0 VDC	
WINDING #1	WINDING #2
254 OHMS ± 10% @ 25° C	254 OHMS ± 10% @ 25° C
6.5 VDC MUST OPERATE	6.5 VDC MUST OPERATE

ENVIRONMENT:

VIBRATION 10 CPS TO 2500 CPS @ 30 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 5 MS MAX.

CONTACT BOUNCE 2.0 MS MAX.

OTHER SPECIFICATIONS IN ACCORDANCE WITH


MIL-R-39016/45

CUST. COMMERCIAL

CUST. NO. M39016/45-014L

TYPE 'LS' RELAY

CUSTOMER DATA SHEET



CONTACT RATING: 2 AMPS 28 VDC

RESISTIVE 100,000 OPERATIONS

DR. R.B. 8/23/94 CK. 8/23/94 Jmb

COMMUNICATIONS INSTRUMENTS, INC.

LS-9514L