


REV. 0
DCO 140912

COIL: @ 25°C
 RESISTANCE 50 OHMS ± 10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC
 MUST RELEASE 1.4 VDC MAX, 0.22 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX
RELEASE TIME 4 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 2/16/99 *CK* 2/16/99

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. C. I. I. STD.
 CUST. NO. _____

TYPE MAD RELAY

MAPD-5