



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	TE Connectivity	Response Date	2018-06-05	Contact Email	cc.wu@te.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	62187-2	Amount	316.50409	Version	-	Identity																												
Manufacturer Item Name	FASTON 187 20-24AWG TPPBR	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Phos Bronze				1.0	312.95723	mg																										
Substance	2	Copper	Supplier	7440-50-8	94.6985	1.0	296.3658	mg																										
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.06259145	mg																										
Substance	2	Chromium	Supplier	7440-47-3	0.01	1.0	0.03129572	mg																										
Substance	2	Tin	Supplier	7440-31-5	4.5	1.0	14.08308	mg																										
Substance	2	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.01564786	mg																										
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	0.31296	mg																										
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.03129572	mg																										
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00312957	mg																										
Substance	2	Zinc	Supplier	7440-66-6	0.3	1.0	0.93887	mg																										
Substance	2	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.31296	mg																										
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.31296	mg																										
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.01564786	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.15648	mg																										
Substance	2	Nickel	Nickel	7440-02-0	0.1	1.0	0.31296	mg																										
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00156479	mg																										
Material	1	Tin Plate				1.0	3.54686	mg																										
Substance	2	Tin	Supplier	7440-31-5	99.73	1.0	3.53728	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00709372	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0024828	mg																										