



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-20-003852	16MAR2020	RK	HD

Component 1 HTAT-32/8


a) Part as supplied



b) Part fully recovered



Component 2 RBK-105-NR5100/A-X



PRODUCT DIMENSIONS & NOTES

DIMENSIONS (in millimetres)

Component 1: HTAT-32/8-0			Component 2: RBK-105-NR5100/A-X				
D	d	T	H	h	L	W1	W2
MIN	MAX	NOM	±20%	±20%	±20%	±20%	±30%
a	b	b					
32.0	8.0	2.54	8.50	6.50	2.75	38.50	1.0
Supplied cut length 65mm ±3.0mm			Supplied cut length 12mm ±0.8mm				
<b>MATERIAL:</b> JACKET: Flame Retarded Modified Polyolefin (Colour: Black) LINER: Hot Melt Adhesive (Colour: Amber)			<b>MATERIAL:</b> Hot Melt Adhesive (Colour: Amber)				

TE Connectivity. All Rights Reserved. © 2015



DIMENSIONS: mm	DWN	HD	11MAR2015	MATERIAL	-	FINISH	-	
	CHK	CD	11MAR2015	TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	CD	11MAR2015					NAME
	0 PLC	± -	PRODUCT SPEC	108-120026	SIZE	A4	CAGE CODE	-
1 PLC	± -	APPLICATION SPEC	-	DRAWING NO	RBK-105-KIT-0110-A0			
2 PLC	± -	WEIGHT	7.04 g	RESTRICTED TO	-			
3 PLC	± -			SCALE	NTS		SHEET	1 of 1
4 PLC	± -			CUSTOMER DRAWING	REV	A1		
ANGLES	± -							