



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-20-006073	26APR20	RK	HD

Component 1 HTAT-32/8


a) Part as supplied



b) Part fully recovered



Component 2 RBK-105-NR5100/A-X



PRODUCT DIMENSIONS & NOTES

DIMENSIONS (in millimetres)

Component 1: HTAT-32/8-0			Component 2: RBK-105-NR5100/A-X				
D	d	T	H	h	L	W1	W2
MIN	MAX	NOM	±20%	±20%	±20%	±20%	±30%
a	b	b					
32.0	8.0	2.55	8.50	6.50	2.75	38.50	1.0
Supplied cut length 60mm ±3.0mm			Supplied cut length 12mm ±0.8mm				
MATERIAL: JACKET: Flame Retarded Modified Polyolefin (Colour: Black) LINER: Hot Melt Adhesive (Colour: Amber)			MATERIAL: Hot Melt Adhesive (Colour: Amber)				

TE Connectivity. All Rights Reserved. © 2015



DIMENSIONS: mm	DWN	HD	03MAR2015	MATERIAL	-	FINISH	-
	CHK	CD	03MAR2015	TE TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	CD	03MAR2015				
0 PLC ± -	PRODUCT SPEC			NAME			
1 PLC ± -	108-120026			RBK-105-KIT-0510-A0			
2 PLC ± -	APPLICATION SPEC			-			
3 PLC ± -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
4 PLC ± -	A4	-	© RBK-105-KIT-0510-A0	-			
ANGLES ± -	WEIGHT			SCALE			
	6.14g			NTS		SHEET 1 OF 1	
CUSTOMER DRAWING				REV A2			