



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER ECR-20-005865	22APR2020	RK	HD

Component 1 HTAT-12/3-0


a) Part as supplied



b) Part fully recovered



Component 2 RBK-105-NR5020/A-X



PRODUCT DIMENSIONS & NOTES

DIMENSIONS (in millimetres)

Component 1: HTAT-12/3-0			Component 2: RBK-105-NR5020/A-X				
D	d	T	H	h	L	W1	W2
MIN	MAX	NOM	±20%	±20%	±20%	±20%	±30%
a	b	b					
12.0	3.0	1.4	8.55	6.50	2.75	8.50	1.0
Supplied cut length 25mm ±1.5mm			Supplied cut length 8mm ±0.8mm				
MATERIAL: JACKET: Flame Retarded Polyolefin (Colour: Black) LINER: Hot Melt Adhesive (Colour: Clear)			MATERIAL: Hot Melt Adhesive (Colour: Amber)				

TE Connectivity. All Rights Reserved. © 2013



DIMENSIONS: mm	DWN	28AUG2013	MATERIAL	-	FINISH	-
	CHK	16SEP2013	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	16SEP2013				
	CD		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -	PRODUCT SPEC	108-120026	A4	-	© RBK-105-KIT-2402-A0	-
1 PLC ± -	APPLICATION SPEC	-	WEIGHT	0.79g	CUSTOMER DRAWING	SCALE NTS
2 PLC ± -						SHEET 1 OF 1
3 PLC ± -						REV A2
4 PLC ± -						
ANGLES ± -						

