


T-DR-25-NR1-***H

a) Part as supplied



Thickness = 0.60 ±0.15
{0.024 ± 0.006}

DIMENSIONS (in millimetres) {inches}

Part No.	L ±10%	T ±10%	W ±10%	X ±10%	Y ±10%
T-DR-25-NR1-50H	50 {1.97}	3.0 {0.12}	25 {1.00}	9.7 {0.38}	6.3 {0.25}
T-DR-25-NR1-75H	75 {2.95}	3.0 {0.12}	25 {1.00}	9.7 {0.38}	6.3 {0.25}
T-DR-25-NR1-100H	100 {3.94}	3.0 {0.12}	25 {1.00}	9.7 {0.38}	6.3 {0.25}
T-DR-25-NR1-125H	125 {4.92}	3.0 {0.12}	25 {1.00}	9.7 {0.38}	6.3 {0.25}
T-DR-25-NR1-150H	150 {5.92}	3.0 {0.12}	25 {1.00}	9.7 {0.38}	6.3 {0.25}

Copyright (!)

Urheberrechte

The copyright in this drawing is the property of Raychem Ltd. The drawing is issued on condition that it is not copied, reproduced or disclosed to a third party, either in whole or in part without the prior written consent of Raychem Ltd.

Drawn A.LILLEY. Checked *[Signature]* Issue 1 Date July 1998

Conforms to ISO Recommendations
3rd Angle Projection
Not to Scale

Approval
Design

MKTG. *[Signature]*

Q.A. *[Signature]*

