

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW
	B1	ECR-23-181096	18JUL2023	BS	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
 INSULATION MATERIAL: PC
 RATED VOLTAGE: 830V
 RATED CURRENT: 40A
 INSULATION RESISTANCE: $\geq 400M\Omega$
 RATED IMPULSE VOLTAGE: 8KV
 POLLUTION DEGREE: 3
 FLAMMABILITY: UL94V-0
 MATING CYCLES: 500 CYCLES
 WIRE RANGE: 1.0~6.0mm² / 8AWG(10mm²)
 CAUTION, INSULATOR OF 8AWG(10mm²) CABLE $\leq \varnothing 6.1mm$.
 BREAK THE INSERT TO REMOVE 8AWG(10mm²) CONTACTS.


CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
 (ORDER No. REFER TO DRAWING:T20400X20XX000)

注释:


1. 技术参数:
 绝缘材料: PC
 额定电压: 830V
 额定电流: 40A
 绝缘电阻: $\geq 400M\Omega$
 脉冲电压: 8KV
 污染等级: 3
 阻燃等级: UL94V-0
 插拔次数: 500次
 接线范围: 1.0~6.0mm² / 8AWG(10mm²)
 注意, 8AWG(10mm²) 线缆绝缘直径 $\leq \varnothing 6.1mm$.
 退出 8AWG(10mm²) 针时需要破坏芯件.

接线类型: 冷压接

2. 端子需要单独订购.
 (订货号参考图面: T20400X20XX000)

T2111042201-007	HMN-004-F	HMN-004 FEMALE MODULE INSERT HMN-004 模块母插	
PART NUMBER 料号		PART DESCRIPTION 描述	
DWN 19SEP2017 YORK CHEN		 TE Connectivity	
CHK 19SEP2017 GINO YAO			
APVD 19SEP2017 CHRIS WANG			
PRODUCT SPEC 108-137060			
APPLICATION SPEC 114-137060		NAME HMN-004-F	
WEIGHT -		SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING		DRAWING NO T2111042201007	RESTRICTED TO -
		SCALE 3:2	SHEET 1 OF 1
			REV B1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC \pm -
	1 PLC \pm -
	2 PLC \pm -
	3 PLC \pm -
	4 PLC \pm -
	ANGLES \pm -
MATERIAL	FINISH
-	-
-	-

1470-19 (3/13)