

Table 1: Dimensions Millimeters (Inches)

| Size | (A) | (B) Minimum | (L) Nominal | (C) Minimum | (D) Maximum | (W) |
|---------|--------------------------|----------------|----------------|----------------|----------------|--------------------------|
| TC 4001 | 19.1(0.750) ± 1.6(0.062) | 10.2(0.400) | 3.8(0.15) | 1.6(0.63) | 0.8(0.030) | 0.51(0.020) ± 0.1(0.005) |
| TC 4003 | 25.4(1.000) ± 1.6(0.062) | 14(0.550) | 3.8(0.15) | 3.2(0.125) | 1.3(0.050) | 0.64(0.025) ± 0.1(0.005) |
| TC 4005 | 28.6(1.125) ± 1.6(0.062) | 14(0.550) | 3.8(0.15) | 6.4(0.250) | 2.5(0.100) | 0.69(0.027) ± 0.1(0.005) |

Color: TC4001 White
TC4003 Red
TC4005 Gray


Reference Specification TEC-108-120013

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 2017 TE Connectivity

| | | | | |
|---|-----------------------|-----------|--|--------------------|
| DIMENSIONS: mm | DWN J. Bitter | 29-NOV-16 | MATERIAL - | FINISH - |
| | CHK - | - |  TE Connectivity 305 Constitution Drive Menlo Park, CA 94025 USA | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - | APVD - | - | | |
| | PRODUCT SPEC - | - | SIZE A4 | CAGE CODE 06090 |
| | APPLICATION SPEC - | - | DRAWING NO TC-CAPS | RESTRICTED TO - |
| | WEIGHT 0 | | SCALE None | SHEET 1 of 1 |
| CUSTOMER DRAWING | | | REV D | |