



TruBlue 255 Level Data logger

±0.05% FS TEB Level Accuracy

Stainless Steel or Titanium Construction

<1cm Accuracy Error up to 10m H₂O

Calibration Report with Each Instrument

Ten Year Permanent Battery

Standard 8 MB Internal Memory for up to 550,000 Data Points

Optional 56 MB Internal Memory for up to 3.7 Million Data Points

Optional Battery Pack for Rapid Sampling

User-friendly TruWare Software Included Free of Charge

High Speed Data Retrieval

Two Year Warranty