

D E S C R I P T I O NPRODUCT COVERED:

Pressure Cable Connectors - Type ECV.
(See Ill. 2 for individual cat. nos.).

ENGINEERING CONSIDERATIONS:

The connectors comply with UL 486C First Edition.

Marking - In addition to the marking indicated in the report, the unit container or stuffer sheet indicates "Twist wires together before crimping," or similar statement. The unit containers shall be marked "TO BE SOLD ONLY WITH INSTALLATION INSTRUCTIONS".

The insulated pressure cable connectors covered by this report are rated 600 V max for use in building wiring and 1000 V max for use in fixtures and signs. They are for use in locations where the temperature does not exceed 105°C. The connectors are assembled to combinations of copper wire by means of this manufacturer's hand or power tooling. (See Ill. 2 for the proper tooling and wire combinations)