

# MIL-STD-1760 Type 1

## Stores Management Systems

The 1760 Type 1 range of connectors is designed to meet the electrical interface requirements of MIL-STD-1760.

The first tri-start threaded plug and lanyard release plugs can be used between aircraft and pylon.

For applications which require instant disconnection the lanyard release plug offers a viable solution.



### FEATURES

- Tri-Start threaded plugs
- Lanyard release
- Shortened length lanyard release plug available
- Complies with MIL-DTL-38999 Series III
- Full environmental performance

### COMPANY QUALITY APPROVALS

- Civil Aviation Authority A8-1
- BS EN ISO 9001
- Military Spec Approvals 38999
- BS9000 and CECC
- Underwriters Laboratories

**With 30 years experience in designing and manufacturing at its own facilities, Deutsch UK can provide interconnection solutions for the most demanding of environments**

### BENEFITS

- Easy connection
- Instant disconnection through lanyard release

### GENERAL SPECIFICATION

<b>Material:</b>	
Shell/coupling ring:	Aluminium Alloy
Plating:	Cadmium plate olive drab over nickel
<b>Contacts:</b>	
Material:	Gold plated Copper Alloy
Type:	Crimp
<b>Insulators:</b>	Thermoplastic
<b>Interface Seal:</b>	Fluorinated Silicone
<b>Temperature:</b>	-55°C to +175°C
<b>Durability:</b>	No electrical or mechanical defects after 500 cycles
<b>Vibration:</b>	As per MIL-DTL-38999
<b>Thermal Shock:</b>	As per MIL-DTL-38999

Deutsch UK  
Castleham Industrial Estate  
4 Stanier Road, St Leonard-On-Sea  
East Sussex TN38 9RF England


Telephone +44 (0) 1424 852721  
Fax +44 (0) 1424 851726

Email [marketinguk@deutsch.net](mailto:marketinguk@deutsch.net)  
[www.deutsch.net](http://www.deutsch.net)




DEUTSCH


## ORDERING INFORMATION - DEUTSCH PART NUMBER



## MILITARY NUMBER - STANDARD PLUGS/RECEPTACLES



## MILITARY NUMBER - LANYARD RELEASE PLUGS



For further options of Lanyard Release and Snatch Connectors please consult Deutsch

## CONTACTS, TOOLING & FILLER PLUGS

NB: Filler plugs must be ordered separately as they are not supplied with the connectors

Contact Size & Type	Deutsch Part Number	Military Spec. Part Number	Crimping Tool	Crimping Tool Locator	Insert/Extract Tool	Filler Plugs
20 Pin	39841-20	M39029/58-363	M22520/1-01	M22520/1-04	M18969/14-02	600300-20
20 Socket	39843-20	M39029/56-351	M22520/1-01	M22520/1-04	M18969/14-02	600300-20
16 Pin	39841-16	M39029/58-364	M22520/1-01	M22520/1-04	M18969/14-03	600300-16
16 Socket	39843-16	M39029/56-352	M22520/1-01	M22520/1-04	M18969/14-03	600300-16
12 Shielded Pin	62290-211	M39029/28-211	Inner M22520/2-01	M22520/2-34	M18969/14-04	602064
12 Shielded Socket	602272-416	M39029/75-416	Outer M22520/31-01	M22520/31-02	M18969/14-04	602065
12 Coax Pin	602177	M39029/102-558	Inner Soldered	Not applicable	M18969/14-04	602064
12 Coax Socket	602176	M39029/103-559	Outer M22520/5-01	M2252/5-03	M18969/14-04	602065
10 Pin	602078-10	M39029/58-528	1716 P-I	Integral with tool	M18969/14-05	602068
10 Socket	602079-10	M39029/56-527	DMC	Integral with tool	M18969/14-05	602068
8 Twinax Pin	602081-A-9734*	M39029/90-529	Ctr M22520/2-01 Int M22520/5-01	K709 Y631 Close B	M18969/14-06	602066
8 Twinax Socket	602091-A-9734	M39029/91-530	Outer M22520/5-01	Y631 Close A	M18969/14-06	602067
8 Twinax Pin (Speedy Crimp)	602080-A-9734*	Awaiting allocation	Ctr TDB-CT-08 Int TDB-CT-08 Outer M22520/5-01	Integral with tool	M18969/14-06	602066
8 Twinax Socket (Speedy Crimp)	602090-A-9734*			Integral with tool	M18969/14-06	602067
8 Twinax Socket (Speed Crimp Short-Lenght)	60269-A-9734*			Y631 Close A	M18969/14-06	602067

\* MOD 9734 - Includes Contact sealing boot