

Wire Seal Options N = Normal wire seals (green ring) T = Thin wall wire seals (gray ring) N = Configurations N = Normal wire seals (green ring) XX-XX X | Size XX X | Number and Size of Cavities

18 Shell Size Configurations

E = Extra thin wall wire seals (blue ring)



18-6 2 size 4, 4 size 16 N, E



18-8 8 size 12 **N, E**



18.14 14 size 16 **N, T, E**



18-20 2 size 16, 18 size 20 N, E



18-21 21 size 20

24 Shell Size Configurations



24-7 (-C038 only) 3 size 4+, 4 size 16 N



24-91 size 4, 2 size 8,
6 size 12 **N, E**



24-14 1 size 4, 1 size 12, 12 size 16 **N, E**



24-16 16 size 12 **N, E**



24-18 1 size 8, 3 size 12, 14 size 16 **N, E**



24-19 6 size 12, 13 size 16 **N, E**



24-21 4 size 12, 17 size 16 **N, E**



24-23 23 size 16 **N, T, E**



24-294 size 12, 19 size 16,
6 size 20

E*



24-31 31 size 16 **T*, E***



24-19 6 size 12, 13 size 16 **N, E**



24-21 4 size 12, 17 size 16 **N, E**



24-23 23 size 16 **N, T, E**



24-294 size 12, 19 size 16,
6 size 20



31 size 16 **T*, E***



24-33 33 size 20 N



24-35 3 size 16, 32 size 20 **N, E**



24-47 5 size 16, 42 size 20



24-91-P064*** 2 size 8, 2 size 12, 5 size 16 **N, E**


^{*} Requires size 4 contact part numbers, 5960-203-04** (pin) and 5962-203-4** (socket)

^{*} Modified seal, see drawing


^{***} Without P064 modification, plug cavities 4 and 5 are internally connected




Canfiaurations



18 Shell Size Configurations



24 Shell Size Configurations



[†]Requires size 4 contact part numbers, 5960-203-04**(pin) and 5962-203-04**(socket)

^{*}Modified seal, see drawing *Without P064 modification, plug cavities 4 and 5 are internally connected