

强制性认证产品符合性自我声明




自我声明编号：2020960307002489

泰科电子（深圳）有限公司（生产者）确认知晓《强制性产品认证自我声明实施规则》以及相关产品强制性认证实施规则的要求，对本声明承担全部法律责任。

泰科电子（深圳）有限公司（生产者）声明以下产品已按照《强制性产品认证自我声明实施规则》以及相关产品强制性认证实施规则的要求进行检测，符合相关标准要求；自本声明签署之日起，生产和销售的产品持续符合以下标准与实施规则的要求；保存本声明涉及的技术文档至少10年；正确使用强制性产品认证标志；如产品或其符合性信息发生变更，将及时更新技术文档并报送产品变更信息。

生产者名称：泰科电子（深圳）有限公司
生产者地址：广东省深圳市宝安区石岩街道泰科电子科技园
依据的强制性产品认证规则：强制性产品认证实施规则自我声明
产品名称：设备用断路器
产品系列、型号、规格：(见附页)
依据的标准：GB/T17701-2008
生产企业名称：乔日电业制品（东莞）有限公司
生产企业地址：广东省东莞市虎门镇路东村

联系人：高伟
电话：0755-27620888-106
电子邮箱：wei.gao@te.com
指定签字人：

自我声明时间：2020-10-09
自我声明地点：广东省深圳市

生产者签章：

注：有关本声明信息真伪可登录全国认证认可信息公共服务平台（cx.cnca.cn）或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020960307002489

产品系列、型号、规格:

W54 Series, W57 Series (型号解释详见附件)

); Ue: 125/250VAC In: 5A, 6A, 7A, 8A, 9A, 10A, 11A, 12A, 13A, 14A, 15A, 16A, 17A, 18A, 20A, 25A, 28A, 30A (W54 Series)

5A, 6A, 7A, 8A, 9A, 10A, 11A, 12A, 13A, 14A, 15A, 16A, 17A, 18A, 20A (W57 Series); 操作方式: R-type; Incl: 1000A; 极数: 1P

联系人: 高伟
电话: 0755-27620888-106
电子邮箱: wei.gao@tcc.com
指定签字人:

自我声明时间: 2020-10-09

自我声明地点: 广东省深圳市

生产者签章:



注: 有关本声明信息真伪可登录全国认证认可公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020960307002489

产品系列、型号、规格(附件):

型号的解释 (Explanation of model/ type):

1) W54 型号的解释

W	54	X	B	1	A	4	A	1	0	5	
A	B	C	D	E	F	G	H	I	J	K	L

- A. DESIGNATOR:
*W - CIRCUIT BREAKER
- B. SERIES NUMBER
*54 = SINGLE POLE,PUSH TO RESET
- C. CIRCUIT FUNCTION:
*X = SERIES TRIP
*F - SERIES TRIP-CADMIUM FREE CONTACTS
- D. BUTTON:
*A = (2) WHITE WITH NO RATE MARKING
*B = (4) WHITE WITH RED RATE MARKING(VERTICAL) VIEW B
*C = (5) WHITE WITH BLACK RATE MARKING(VERTICAL) VIEW B
D - (1) BLACK
E = (6) BLACK WITH WHITE RATE MARKING(HORIZONTAL) VIEW A
F - (7) WHITE WITH RED RATE MARKING (HORIZONTAL) VIEW A
G = (8) WHITE WITH BLACK RATE MARKING (HORIZONTAL)VIEW A
H - (3) BLACK WITH WHITE RATE MARKING (VERTICAL) VIEW B
I = (9) RED
- E. MOUNTING BUSHING
*1 = (2) 9.8MM x 12.6MM LONG (B TYPE) (M11x1,DOUBLED)
2 = (6) 3/8" (ONE SIDE FLAT FACE) x10MM LONG
3 = (4) A TYPE (M11x1,DOUBLED)
4 = (8) D TYPE (M12x1,DOUBLED)
PLASTIC:
6 = (5) A TYPE (M11x1,DOUBLED)
*7 = (7) C1 TYPE (3/8"x24,D)
8 - (9) SNAP IN II
- F. TERMINALS:
*A = (1) QUICK CONNECT .250"(6.35MM) STRAIGHT
*B = (6) QUICK CONNECT .250"(6.35MM) BENT 90°
*C = (D) #8/32 SCREW BENT 90°-HARDWARE INSTALLED
D = (2) .250 TAB BENT 45°

W	54	X	B	1	A	4	A	1	0	5	
A	B	C	D	E	F	G	H	I	J	K	L

联系人: 高伟
 电话: 0755-27620888-106
 电子邮箱: wei.gao@tsg.com
 指定签字人:

自我声明时间: 2020-10-09
 自我声明地点: 广东省深圳市

生产者签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx. cnca. cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020960307002489

产品系列、型号、规格(附件):

- E = (7) 250 TAB BENT 90°BACKWARDS
 - F = (A) #8/32 SCREW BENT 45°-HARDWARE INSTALLED
 - G = 1 QC.250°AND 1 #8/32 SCREW BENT 90°-HARDWARE INSTALLED
 - G. MOUNTING HARDWARE:
 - METAL:
 - *4 = (9) KNURLED NUT/HEX NUT
 - 6 = HEX NUT
 - *12 = (4) KNURL NUT
 - 15 = 2 HEX NUT , 1 LOCK WASHER
 - 18 = 1 HEX NUT , 1 LOCK WASHER
 - *99 = (0) NONE
 - PLASTIC:
 - *5 = KNURLNUT
 - 7 = INTEGRATED KNURL NUT
 - 8 = INTEGRATED KNURLNUT W/
SMALL HOLE
 - 22=PLASTIC KNURLFD NUT
W / METAL LOCK WASHER
 - H. MOUNTING HARDWARE PACKAGE:
 - *A = (0) ASSEMBLED TO BUSHING
 - *B = (1) BULK UNASSEMBLED
 - *C = NO MOUNTING HARDWARE
 - I. VOLTAGE:
 - *1 = 250VAC
 - 2 = 125VAC/50VDC
 - J. NAMEPLATE: (FIGURE 4, page F2)
 - *0 = NONE
 - 1 = EMBOSSED ALUMINUM
 - 2 = SILVER PRINTING ON BLACK
 - 3 = BLACK PRINTING ON SILVER
 - K. AMPERE RATING:
 - 5A,6A,7A,8A,9A,10A,11A,12A,13A,14A,15A, 16A,17A,18A,20A,25A,28A,30A
 - L. OPTIONNS:
 - M=MEETS UL1500 REQUIREMENTS
 - W=WELDED CONTACTS
- 2) W57型号的解释
- | | | | | | | | | | | | |
|---|----|---|---|---|---|---|---|---|---|---|---|
| W | 57 | X | A | 2 | A | 7 | B | 1 | 0 | 5 | |
| A | B | C | D | E | F | G | H | I | J | K | L |
- A. DESIGNATOR:
 - *W = CIRCUIT BREAKER
 - B. SERIES NUMBER:
 - *57 = SINGLE POLE,PUSH TO RESET

联系人: 高伟
电话: 0755-27620888-106
电子邮箱: wei.gao@tcc.com
指定签字人:

自我声明时间: 2020-10-09
自我声明地点: 广东省深圳市
生产者签章:

注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020960307002489

产品系列、型号、规格(附件):

- C. CIRCUIT FUNCTION:
*X = SERIES TRIP
- D. BUTTON:
*A = (2) WHITE WITH NO RATE MARKING
*B = (4) WHITE WITH RED RATE MARKING(VERTICAL) VIEW B
*C = (5) WHITE WITH BLACK RATE MARKING(VERTICAL) VIEW B
D = (1) BLACK
E = (6) BLACK WITH WHITE RATE MARKING(HORIZONTAL) VIEW A
F = (7) WHITE WITH RED RATE MARKING (HORIZONTAL) VIEW A
G = (8) WHITE WITH BLACK RATE MARKING (HORIZONTAL) VIEW A
H = (3) BLACK WITH WHITE RATE MARKING (VERTICAL) VIEW B
I = (9) RED
J = 黑色,无印刷安培数推杆,安培数印於下盖两端子之间.
- E. MOUNTING BUSHING:
PLASTIC:
*1 = (3) 9.8MM x 9.6MM LONG(B TYPE) (M11x1,DOUBLED)
*2 = (7) 3/8" (ONE SIDE FLAT FACE) x10.5MM LONG(C1 TYPE) (3/8"x24.D)
4 = (9) SNAP IN II
METAL:
5 = (4) A TYPE (M11x1,DOUBLED)
*6 = (6) C1 TYPE (3/8"x24.D)
*7 = (8) D TYPE (M12x1,DOUBLED)
8 = (A) C2 TYPE (3/8"x24,DOUBLED)
- F. TERMINALS:
*A = (1) QUICK CONNECT .250"(6.35MM) STRAIGHT (A TYPE)
*B = (5) QUICK CONNECT .250" 90°BEND (E TYPE)
C = (2) B TYPE
D = (3) C TYPE

W 57 X A 2 A 7 B 1 0-5 L
A B C D E F G H I J K L

- E = (4) D TYPE (PCB COMPATIBLE)
- F = (6) F TYPE (PCB COMPATIBLE)
- G = (8) H TYPE
- H = 1 QC .250" AND 1 #8/32 SCREW BENT 90°-HARDWARE INSTALLED
- I = F TYPE (PCB COMPATIBLE) AMPERAGE REVERSED VIEW C
- G. MOUNTING HARDWARE:
METAL:
*4 = (9) KNURLED NUT/HEX NUT
6 = HEX NUT
*12 = (4) KNURLNUT
PLASTIC:
*5 = KNURLNUT
7 = INTEGRATED KNURLNUT
8 = INTEGRATED KNURLNUT

联系人: 高伟
电话: 0755-27620888-106
电子邮箱: wei.gao@te.com
指定签字人:

自我声明时间: 2020-10-09
自我声明地点: 广东省深圳市
生产者签章:

注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)

自我声明编号: 2020960307002489



产品系列、型号、规格(附件):

- W / SMALL HOLE
22=PLASTIC KNURLED NUT
W / METAL LOCK WASHER
- 15 = 2 HEX NUT , 1 LOCK WASHER
18 = 1 HEX NUT , 1 LOCK WASHER
*99 = (0) NONE
- H. MOUNTING HARDWARE PACKAGE:
*A = (0) ASSEMBLED TO BUSHING
*B = (1) BULK UNASSEMBLED
*C = NO MOUNTING HARDWARE
- I. VOLTAGE:
*1 = 250VAC
2 = 125VAC/50VDC
- J. NAMEPLATE:
*0 = NONE
1 = EMBOSSED ALUNINUM
2 = SILVER PRINTING ON BLACK
3 = BLACK PRINTING ON SILVER
- K. AMPERE RATING:
5A,6A,7A,8A,9A,10A,11A,12A,13A,14A,15A, 16A,17A,18A,20A
- L. OPTIONNS:
M=MEETS UL1500 REQUIREMENTS

联系人: 高伟
电话: 0755-27620888-106
电子邮箱: wei.gao@te.com
指定签字人:

自我声明时间: 2020-10-09
自我声明地点: 广东省深圳市

生产者签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。