



# 产品认证证书

证书编号: CQC03001007764

发证日期: 2022年02月28日

有效期至: 长期有效

**委托人名称** 泰科电子(深圳)有限公司  
**及注册地址** 深圳市宝安区石岩街道泰科电子科技园

**制造商名称** 泰科电子(深圳)有限公司  
**及注册地址** 深圳市宝安区石岩街道泰科电子科技园

**生产企业名称** 泰科电子(深圳)有限公司  
**及生产地址** 深圳市宝安区石岩街道泰科电子科技园

**产品名称和系列、规格、型号** 继电器  
OJ, OJE 系列, T77 系列, 产品描述见附件; 仅适用于海拔 5000 米及以下

**产品标准和技术要求** GB/T 21711.1-2008;GB/T 15092.1-2020;GB/T 15092.101-2020

**认证模式** 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-462155-2010;CQC11-462151-2015 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2003 年 10 月 10 日

本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 ( www.cnca.gov.cn ) 查验证书信息



签发: 谢肇煦



中国质量认证中心



# 产品认证证书

证书编号: CQC03001007764

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

型号命名规则:

OJ(E)	-**	-1	**	****	*	-*	*****
代码: 6 位数字或字母代码							
<b>R: 回流焊型(LCP 材料用做外壳和基座) 或空白</b>							
绝缘等级: 空白或 F 或 WG: F 级 155							
触点额定值及材料: HM: 10A 250VAC/30VDC, AgCdO(welding contact); HM2: 10A 250VAC/30VDC, AgSnO(welding contact); LMH: 8A 250VAC/30VDC, AgCdO; LMH2: 8A 250VAC/30VDC、10A/5A 250VAC, AgSnO; DM: 5A 250VAC/30VDC, Ag, AgNi; LM: 3A 250VAC/30VDC, Ag, AgNi; HM5: 10A 250VAC/30VDC, AgCdO(rivet contact); HM6: 10A 250VAC/30VDC, AgSnO(rivet contact)							
线圈电压: 03:3V 05:5V 06:6V 09:9V 12:12V 18:18V 24:24V 48:48V							
极数: 1: 单极							
密封结构: SS: 有通气孔; SH: 外亮点胶密封							
产品基本型号: OJ, OJE							

T77	*	1	D	*	_*	*	_*	*****
代码: 6 位数字或字母代码								
<b>R: 回流焊型(LCP 材料用做外壳和基座) 或空白</b>								
绝缘等级: 空白或 F 或 WG: F 级 155								
线圈电压: 03:3V 05:5V 06:6V 09:9V 12:12V 18:18V 24:24V 48:48V								
触点等级: 3: 3A; 5: 5A; 10: 10A								
线圈类型: D: 直流线圈								
极数: 1: 单极								
密封结构: V: 有通气孔; S: 外亮点胶密封								
产品基本型号: T77								



## 中国质量认证中心



# CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC03001007764

Valid from: Feb.28,2022

Valid until:long-term

**NAME AND REGISTERED ADDRESS OF THE APPLICANT** Tyco Electronics (shenzhen) Co., Ltd  
Tyco Electronics Technology Park,Shiyan Town,Baoan District,Shenzhen, Guangdong, P.R.China

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER** Tyco Electronics (shenzhen) Co., Ltd  
Tyco Electronics Technology Park,Shiyan Town,Baoan District,Shenzhen, Guangdong, P.R.China

**NAME AND LOCATION OF THE FACTORY** Tyco Electronics (shenzhen) Co., Ltd  
Tyco Electronics Technology Park,Shiyan Town,Baoan District,Shenzhen, Guangdong, P.R.China

**PRODUCT NAME, MODEL AND SPECIFICATION** Relay  
OJ, OJE 系列, T77 系列, 产品描述见附件; 仅适用于海拔 5000 米及以下

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS** GB/T 21711.1-2008;GB/T 15092.1-2020;GB/T 15092.101-2020

**TYPE OF CERTIFICATION SCHEMES** Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462155-2010;CQC11-462151-2015.

Date of original issued: Oct.10,2003

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



# CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC03001007764

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

## 型号命名规则:

OJ(E)	-**	-1	**	****	*	-*	*****
代码: 6 位数字或字母代码							
<b>R: 回流焊型(LCP 材料用做外壳和基座) 或空白</b>							
绝缘等级: 空白或 F 或 WG: F 级 155							
触点额定值及材料: HM: 10A 250VAC/30VDC, AgCdO(welding contact); HM2: 10A 250VAC/30VDC, AgSnO(welding contact); LMH: 8A 250VAC/30VDC, AgCdO; LMH2: 8A 250VAC/30VDC、10A/5A 250VAC, AgSnO; DM: 5A 250VAC/30VDC, Ag, AgNi; LM: 3A 250VAC/30VDC, Ag, AgNi; HM5: 10A 250VAC/30VDC, AgCdO(rivet contact); HM6: 10A 250VAC/30VDC, AgSnO(rivet contact)							
线圈电压: 03:3V 05:5V 06:6V 09:9V 12:12V 18:18V 24:24V 48:48V							
极数: 1: 单极							
密封结构: SS: 有通气孔; SH: 外壳点胶密封							
产品基本型号: OJ, OJE							

T77	*	1	D	*	**	*	-*	*****
代码: 6 位数字或字母代码								
<b>R: 回流焊型(LCP 材料用做外壳和基座) 或空白</b>								
绝缘等级: 空白或 F 或 WG: F 级 155								
线圈电压: 03:3V 05:5V 06:6V 09:9V 12:12V 18:18V 24:24V 48:48V								
触点等级: 3: 3A; 5: 5A; 10: 10A								
线圈类型: D: 直流线圈								
极数: 1: 单极								
密封结构: V: 有通气孔; S: 外壳点胶密封								
产品基本型号: T77								



CHINA QUALITY CERTIFICATION CENTRE