



PRODUCT CERTIFICATE

No.: CQC16002154262

NAME AND ADDRESS OF THE APPLICANT

Tyco Electronics Austria GmbH
Schrackstrasse 1 3830 Waidhofen / Thaya Austria

NAME AND ADDRESS OF THE MANUFACTURER

Tyco Electronics Austria GmbH
Schrackstrasse 1 3830 Waidhofen / Thaya Austria

NAME AND ADDRESS OF THE FACTORY

Tyco Electronics EC Trutnov s.r.o. (V024246)
Komenského 821 CZ-541 83 Trutnov Czech Republic

NAME, MODEL AND SPECIFICATION

Relay

RY series, Contact load: 8A 250VAC, Coil: 5VDC, 6VDC, 9VDC, 10VDC, 12VDC, 15VDC, 18VDC, 19VDC, 21VDC, 24VDC, 32VDC, 36VDC, 48VDC, 60VDC; 0.245W; Electrical endurance: 100000 cycles (AgCdO, AgNi contact); 50000 cycles (AgSnO contact); Ambient temperature: Mechanical endurance: 200000 cycles; Ambient temperature: 40°C ~ 70°C; RTII, RTIII, Series description see the annex

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T21711.1-2008

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-462155-2010.

Date of issue: Nov.01,2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President: _____

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0091084



产品认证证书

证书编号: CQC16002154262

申请人名称及地址

泰科电子(奥地利)股份有限公司
Schrackstrasse 1 3830 Waidhofen / Thaya Austria

制造商名称及地址

泰科电子(奥地利)股份有限公司
Schrackstrasse 1 3830 Waidhofen / Thaya Austria

生产企业名称及地址

Tyco Electronics EC Trutnov s.r.o. (V024246)
Komenského 821 CZ-541 83 Trutnov Czech Republic

产品名称和系列、规格、型号

继电器

RY 系列, 触电负载: 8A 250VAC; 线圈: 5VDC、6VDC、8VDC、9VDC、10VDC、12VDC、15VDC、18VDC、19VDC、21VDC、24VDC、32VDC、36VDC、48VDC、60VDC; 0.245W; 电气寿命: 10000周期(触点材质AgCdO、AgNi), 5000周期(触点材质AgSnO); 机械寿命: 30000000周期; 环境温度: -40℃ ~ 70℃; RII、RTIII(系列命名方式见证书附件)

产品标准和技术要求

GB/T21711.1-2008

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-462155-2010认证规则的要求, 特发此证。

发证日期: 2016年11月01日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0091084



产品认证证书

附录:

第 1 页 共 1 页

证书编号: CQC16002154262

纸号: 91084

系列命名方式:

	<u>RY</u>	<u>6</u>	<u>1</u>	<u>1</u>	<u>024</u>	<u>####</u>
	I	II	III	IV	V	VI
I 基本型号	RY					
II 密封性和端子距离	2 开孔, 3.2mm 端子距离 5 开孔, 5mm 端子距离(N.O. or N.C. contact) 6 密封, 3.2mm 端子距离 A 密封, 5mm 端子距离(N.O. or N.C. contact)					
III 触点结构	1 C.O. contact 3 N.O. contact 5 N.C. contact					
IV 触点材质	0 AgCdO	Contact mounting construction	Riveted			
	1 AgNi 0,15		Riveted or Welded			
	2 AgNi 0,15 HTV		Riveted or Welded			
	3 AgSnO		Riveted or Welded			
V 线圈电压 (DC)	005.5V/ 006.6V/ 008.8V/ 009.9V/ 012.12V/ 015.15V/ 018.18V/ 019.19V/ 021.21V/ 024.24V/ 032.32V/ 036.36V/ 048.48V/ 060.60V					
VI 代码	4 位数字或字母代码, 产品上可不显示出来 R 回流焊型号 (2 开孔, 3.2mm 端子距离和 5 开孔, 3.2mm 端子距离)					

注: 此附录与证书同时使用时有效。

主任: 



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>