



产品认证证书

证书编号: CQC18002189312

发证日期: 2022年04月28日

有效期至: 长期有效

委托人名称 Tyco Electronics Austria GmbH
及注册地址 Schrackstrasse 1 3830 Waidhofen / Thaya Austria

制造商名称 Tyco Electronics Austria GmbH
及注册地址 Schrackstrasse 1 3830 Waidhofen / Thaya Austria

生产企业名称 泰科电子(深圳)有限公司
及生产地址 深圳市宝安区石岩街道泰科电子科技园

产品名称和系列、规格、型号 继电器
RZ 系列 触点负载:16A 250VAC ; 12A 24VDC ; 线圈: 3VDC、5VDC、6VDC、9VDC、12VDC、15VDC、18VDC、24VDC、28VDC、34VDC、36VDC、48VDC 0.40W~0.43W ; 电气寿命 : 20000 周期(250VAC) , 1000 周期(24VDC) ; 机械寿命 : 200000 周期 ; 环境温度:-40°C ~ 85°C(RZ0 型), -40°C ~ 105°C (RZH 型) ; RTII

产品标准和技术要求 GB/T 21711.1-2008

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-462155-2010 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2018年03月29日

本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心



产品认证证书

证书编号: CQC18002189312

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

型号命名规则:

RZ	0	3	-1	A	4	-D	012	-R	0	0	XXXX	代码: 4 位数字或字母代码 (产品上可表示出来)
												机械特征: 0 或空白-标准型; S- 插座型
												电气特征: 0 或空白-标准型
												封装类型: -R: 加强型防松香
												线圈电压: 3、5、6、9、12、15、18、24、28、 34、36、48VDC, 012-表示 12VDC
												线圈款式: D-直流线圈
												触点材质: 4-AgNi 3-AgSnO ₂
												触点结构: A-A 型 (单刀单掷-常开型)
												极数: 1-1 极
												产品款式: 3-16A, 双端脚 5mm H_16A, 双端脚 5mm, 高性能
												附加型号: 0-标准型 (85°C) H: 高温型 (105°C)
												基本型号: RZ



中国质量认证中心



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC18002189312

Valid from: Apr.28,2022

Valid until:long-term

NAME AND REGISTERED ADDRESS OF THE APPLICANT Tyco Electronics Austria GmbH
Schrackstrasse 1 3830 Waidhofen / Thaya Austria

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER Tyco Electronics Austria GmbH
Schrackstrasse 1 3830 Waidhofen / Thaya Austria

NAME AND LOCATION OF THE FACTORY Tyco Electronics (shenzhen) Co., Ltd
Tyco Electronics Technology Park,Shiyan Town,Baoan District,Shenzhen, Guangdong, P.R.China

PRODUCT NAME, MODEL AND SPECIFICATION Relay
RZ series Contact load: 16A 250VAC,12A 24VDC; coil: 3VDC, 5VDC, 6VDC, 9VDC, 12VDC, 15VDC, 18VDC, 24VDC, 28VDC, 34VDC, 36VDC, 48VDC; 0.40W ~ 0.43W; Electrical Endurance: 20000cycles(250VAC),1000cycles (24VDC); Mechanical endurance:200000cycles; Ambient temperature:- 40°C ~ 85°C(RZ0 series),-40°C ~ 105°C (RZH series) ;RTII Series description see the annex

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 21711.1-2008

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462155-2010.

Date of original issued: Mar.29,2018

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC18002189312

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

型号命名规则:

RZ	0	3	-1	A	4	-D	012	-R	0	0	XXXX	代码: 4位数字或字母代码 (产品上可表示出来)
												机械特征: 0或空白-标准型; S-插座型
												电气特征: 0或空白-标准型
												封装类型: -R: 加强型防松香
												线圈电压: 3、5、6、9、12、15、18、24、28、34、36、48VDC, 012-表示 12VDC
												线圈款式: D-直流线圈
												触点材质: 4-AgNi 3-AgSnO ₂
												触点结构: A-A型(单刀单掷-常开型)
												极数: 1-1极
												产品款式: 3-16A, 双端脚 5mm H_16A, 双端脚 5mm, 高性能
												附加型号: 0-标准型(85℃) H: 高温型(105℃)
												基本型号: RZ



CHINA QUALITY CERTIFICATION CENTRE