



产品认证证书

证书编号: CQC18002196616

发证日期: 2021年01月13日

有效期至: 长期有效

委托人名称 泰科电子(深圳)有限公司
及注册地址 深圳市宝安区石岩街道泰科电子科技园

制造商名称 泰科电子(深圳)有限公司
及注册地址 深圳市宝安区石岩街道泰科电子科技园

生产企业名称 惠州市群创电子有限公司
及生产地址 惠州市惠澳大道惠南高科技产业园金达路13号厂房A栋4楼东侧

产品名称和系列、规格、型号 继电器
ORWH系列 触点负载:10A 250VAC/30VDC(NO);7A 250VAC/30VDC(NC) 线圈:3VDC、5VDC、6VDC、9VDC、12VDC、18VDC、24VDC、48VDC;电气寿命:20000周期(250VAC),10000周期(30VDC),100000周期(ORWH-SS-1**DM1:10A/250VAC/T85);机械寿命:20000周期;环境温度:-30°C~70°C,-30°C~85°C(ORWH-SS-1**DM1);RTII、RTIII系列描述见附件

产品标准和技术要求 GB/T 21711.1-2008

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-462155-2010 认证规则的要求,特发此证。

本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



签发: 陆楠

中国质量认证中心





PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC18002196616

Valid from: Jan.13,2021

Valid until:long-term

NAME AND REGISTERED ADDRESS OF THE APPLICANT Tyco Electronics (shenzhen) Co., Ltd
Tyco Electronics Technology Park,Shiyan Street,Baoan District,Shenzhen, Guangdong, P.R.China

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER Tyco Electronics (shenzhen) Co., Ltd
Tyco Electronics Technology Park,Shiyan Street,Baoan District,Shenzhen, Guangdong, P.R.China

NAME AND LOCATION OF THE FACTORY Huizhou Qunchuang Electronics Co., Ltd.
4F East, A building, No. 13, JinDa Road, HuiNan High-Tech industrial park, HuiAo Road,Huizhou,GuangDong China

PRODUCT NAME, MODEL AND SPECIFICATION Relay
ORWH series : contact : 10A 250VAC/30VDC(NO) ; 7A 250VAC/30VDC(NC) ; coil : 3VDC, 5VDC, 6VDC, 9VDC, 12VDC, 18VDC, 24VDC, 48VDC ; Electrical endurance : 20000 cycles(250VAC), 10000 cycles(30VDC), 100000 cycles(ORWH-SS-DM1:250VAC/10A/T85) ; Ambient temperature : -30°C ~ 70°C,-30°C ~ 85°C(ORWH-SS-DM1) ; RTII、RTIII, see sereis description in annex

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 21711.1-2008

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462155-2010.
The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:



CHINA QUALITY CERTIFICATION CENTRE



产品认证证书

附 录

第 1 页 共 1 页

证书编号: CQC18002196616

纸 号: 459716

型号命名方法:

ORWH	-**	-1	**	D	*	*	*	*****
代码: 6 位数字或字母代码 (产品上可不表示出来)								
绝缘等级: 空白: A 级 105; F: F 级 155								
触点材质: 空白: AgCdO; 1: AgZnO								
触点结构: 空白: C 型 (单刀双掷-转换型); M: A 型 (单刀单掷-常开型)								
线圈功率: D: 一般敏感型 360mW								
线圈电压: 03:3V 05:5V 06:6V 09:9V 12:12V 18:18V 24:24V 48:48V								
极数: 1: 单极								
密封结构: SS: 有通气孔; SH: 外壳点胶密封								
产品基本型号: ORWH								

注: 此附录与证书同时使用时有效。



中国质量认证中心